



Powering Business Worldwide

FireWire® - 3-Port IEEE 1394 Firewire PCI Card

MODEL NUMBER: F201-003

Description

Tripp Lite's IEEE 1394 Firewire 3 Port PCI Card provides your PC with 3 high-speed Firewire ports. Once this card has been installed in your PC you will have a simple and easy way to connect up to three IEEE 1394 Firewire devices. Connecting DV camcorders, hard disk drives, removable drives, scanners, printers, and other 1394 A/V devices including TVs, VCRs and DVDs will be a breeze. Supports data transfer rates up to 400Mb/s. The flexible 3-and-1 design also provides an internal port in case you are using an internal Firewire device such as a hard drive. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Provides 3 active 6-pin Firewire ports
- 3rd port can be internal or external
- Meets IEEE 1394 standards set by the Institute of Electrical and Electronic Engineers
- Provides three fully 1394-compliant ports at 100, 200 and 400 Mbps
- 100% compliant with open host controller interface (OHCI) requirements
- 100% Plug and Play compatible - Devices can be added or removed without restarting the computer
- Supports up to 63 connected Firewire devices
- Peer to Peer communication structure
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Highlights

- Provides 3 active 6-pin Firewire ports
- Meets IEEE 1394 standards set by the Institute of Electrical and Electronic Engineers
- Fully supports version 2.0 of the IEEE 1394 standard for high-speed serial bus communication
- 100% Plug and Play compatible - Devices can be added or removed without restarting the computer
- Supports up to 63 connected Firewire devices

Package Includes

- IEEE 1394 Firewire PCI Card - 3 Port

Specifications

| OVERVIEW | |
|---------------------------------|----------------------|
| UPC Code | 037332096203 |
| Technology | FireWire |
| CONNECTIONS | |
| Number of Ports | 3 |
| Side B - Connector 1 | (3) 6 PIN (FEMALE) |
| PHYSICAL | |
| Color | Silver |
| Cable Length (ft.) | 0 |
| Cable Length (m) | 0.00 |
| Shipping Dimensions (hwd / in.) | 9.50 x 6.50 x 2.50 |
| Shipping Dimensions (hwd / cm) | 24.13 x 16.51 x 6.35 |
| Shipping Weight (lbs.) | 0.66 |
| Shipping Weight (kg) | 0.30 |
| WARRANTY & SUPPORT | |



Powering Business Worldwide

| | |
|--|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
|--|---------------------------|

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.