



Powering Business Worldwide

## 10 outlet, 10ft cord, 3345 joule rating, 3-line coaxial and 1-line tel/modem/ethernet protection - Home/Business Theater Surge Suppressor

MODEL NUMBER: HT1010SAT3



### Highlights

- 10 outlets / 10-ft. cord
- 3345 joule rating
- 3-line coaxial (gold) surge protection
- 1-line tel/modem/network (100BaseT, high-speed) surge protection
- \$250,000 Ultimate Lifetime Insurance (USA and Canada only)

### Package Includes

- HT1010SAT3 Home/Business Theater Surge Suppressor
- 6-ft. gold DSS cable, 6-ft. coaxial cable, 6-ft. phone cord and 6-ft. network cable
- Instruction manual with warranty information

### Description

Tripp Lite's HT1010SAT3 Home/Business Theater Surge Suppressor provides advanced protection--3345 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small-to-medium home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 10 outlets (with transformer spacing and sliding safety covers), 3-line coaxial protection and 1-line tel/modem/Ethernet (100BaseT, high-speed) protection safeguard an entire home/business theater system. \$250,000 Ultimate Lifetime Insuran coverage (USA and Canada only). Includes two diagnostic LEDs, color-coordinated holographic outlet/plug labels, 10-ft. cord with a right-angle plug, 6-ft. gold DSS cable, 6-ft. coaxial cable, 6-ft. phone cord and 6-ft. network cable.

### Features

- 3345 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$250,000 Ultimate Lifetime Insurance (USA and Canada only) covers connected components against surge damage...for life!
- 10 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely spaced outlets accommodate up to 5 transformers
- Sliding safety covers protect against accidental contact
- Color-coordinated, holographic outlet/plug labels match outlets with component power cords
- 3 sets of surge-protected Type F gold coaxial connectors (with included 6-ft. gold DSS cable and 6 ft. coaxial cable) safeguard components on cable, satellite and antenna line
- 1-line tel/modem/Ethernet (100BaseT, high-speed) surge protection (with included 6 ft. phone cord and 6-ft. network cable) safeguards personal video recorders (PVRs) on a single dial-up or Ethernet line. Built-in splitter (1 jack in and 2 jacks out) allows simultaneous connection of two devices sharing a single line
- 10-ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 2 diagnostic LEDs alert user to protection and grounding status
- Keyhole slots provide convenient wall or cabinet mounting
- Master switch provides one-touch power control over all components. Circuit breaker protects against



Powering Business Worldwide

dangerous system overload

- High-impact plastic housing (black) stands up to the most demanding environments
- UL and cUL listed
- Lifetime product warranty

## Specifications

OVERVIEW	
UPC Code	037332120915
INPUT	
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	Yes
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Transformer Accommodation	(8) Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2-position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm protection and grounding status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3345
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	



Powering Business Worldwide

Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line
Network (Ethernet) Protection	Yes
Telephone/DSL Protection	Yes
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	15.00 x 8.50 x 2.50
Shipping Dimensions (hwd / cm)	38.10 x 21.59 x 6.35
Shipping Weight (lbs.)	3.20
Shipping Weight (kg)	1.45
Unit Dimensions (hwd / in.)	2.250 x 12.000 x 5.250
Unit Dimensions (hwd / cm)	4.5 x 29.8 x 12.1
Unit Weight (lbs.)	2.42
Unit Weight (kg)	1.10
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.