

Isobar Audio/Video Power Conditioning Center - Ultimate 2U rack/console power conditioning center for all audio/video components

MODEL NUMBER: HT7300PC



Description

Tripp Lite's HT7300PC Isobar Audio/Video Power Conditioning Center provides ultimate protection (5700 joules) stopping damaging surges and filtering disruptive EMI/RFI line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio; and longer component life spans. Perfect for large home/business theater installations, high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. Features 12 AC outlets arranged in 3 filter banks: Analog, Digital and High Frequency. Four AC outlets are sequenced and individually controllable; IR remote control device included. Dual digital LED displays plus 12 additional LEDs show incoming voltage, current connected equipment load and a variety of operating conditions. Three-line HD-compatible gold coaxial surge protection, 1-line tel/modem protection with built-in splitter (1 line in/2 lines out) and 1-line Ethernet protection safeguard audio/video components on all connections. Metal housing; 2U rackmount/console design with included hardware and removable console feet, 10-ft. power cord with right-angle plug. Includes 6-ft. gold coaxial cable, 6-ft. phone cable and 6-ft. network cable. \$150,000 Ultimate Lifetime Insurance coverage (USA/Canada only).

Features

- 5700-joule surge suppression rating with EMI/RFI line noise filtering helps components perform at their peak (sharper, crisper video; deeper, fuller audio; and longer component life spans)
- Exclusive Isolated Filter Banks eliminate interference between connected components
- 3 built-in filter banks: Analog, Digital, High Current
- Metal housing safely withstands the strongest surges
- 12 surge-protected NEMA 5-15R AC outlets safeguard all audio/video components
- 4 sequenced, individually IR-controllable AC outlets work with either included remote device or user-supplied universal learning IR remote to facilitate orderly system startup and shutdown
- 3 sets of surge-protected, HD-compatible 2.2 GHz Type F gold coaxial connectors safeguard components on cable, satellite and antenna connections; one 6-ft. gold coaxial cable included

Highlights

- 12 AC outlets arranged in three filter banks; 10-ft. power cord
- 4 sequenced, individually controllable AC outlets; IR remote control device included
- 5700-joule surge suppression rating
- 3-line HD-compatible gold coaxial surge protection
- 1-line tel/modem surge protection with built-in splitter; 1-line Ethernet surge protection
- \$150,000 Ultimate Lifetime Insurance (USA/Canada only)

Package Includes

- HT7300PC Isobar Audio/Video Power Conditioning Center
- One hand-held IR remote control device; one 6-ft. gold coaxial cable; one 6-ft. phone cable; one 6-ft. network cable
- Color-coordinated outlet/plug labels
- Hardware for 2U rackmounting
- Instruction manual with warranty information



Powering Business Worldwide



- 1-line tel/modem surge protection safeguards personal video recorders (PVRs) on a single dial-up connection. Built-in splitter (1 jack in/2 jacks out) allows simultaneous connection of two devices sharing a single line; one 6-ft. phone cable included
- 1-line Ethernet surge protection safeguards equipment on a 10/100 Base T network connection; one 6-ft network cable included
- 10-ft. power cord with right-angle NEMA 5-15P plug permits convenient placement anywhere within a home/business theater system
- 2 digital LED displays and 12 additional diagnostic LEDs alert user to input voltage levels, component load levels and 4 operational conditions (power, protection, grounding, selected outlets)
- 2U rackmount or console installation options; rackmount hardware and removable rubber console feet included
- Illuminated master switch provides one-touch power control over all components.
- 15A circuit breaker protects against dangerous system overload
- Fail-safe thermal fusing acts like an additional circuit breaker, shutting down the unit and connected equipment in the event of a catastrophic surge
- Audible alarm immediately alerts user to damaged protection circuitry; perfect for installations where LEDs aren't normally viewed
- Color-coordinated outlet/plug labels match outlets to component power cords for easy identification
- TUV tested to UL standards 1449, 60950 and 962A
- \$150,000 Ultimate Lifetime Insurance covers connected components against surge damage for life! (USA/Canada only)

Specifications

OVERVIEW	
UPC Code	037332134325
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	225000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	Yes
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(12) 5-15R
Circuit Breaker (amps)	12



Powering Business Worldwide



Overload Protection	15A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Illuminated on/off power switch
Audible Alarm	Audible alarm
Diagnostic LED Details	Dual digital LED displays and 12 additional diagnostic LEDs alert user to input voltage levels, component load levels and 4 operational conditions (power, protection, grounding, selected outlets)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	5700
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Safe Thermal Fusing	Yes
UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	Yes
Isolated Filter Banks	3
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	Yes
Telephone/DSL Protection	Yes
PHYSICAL	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Form Factors Supported	2U rackmount; console installation
Housing Color	Black
Included Mounting Accessories	2U rackmount hardware
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	5.50 x 20.50 x 16.50
Shipping Dimensions (hwd / cm)	13.97 x 52.07 x 41.91
Shipping Weight (lbs.)	16.00



Powering Business Worldwide



Shipping Weight (kg)	7.26
Unit Dimensions (hwd / in.)	3.500 x 17.250 x 12.500
Unit Dimensions (hwd / cm)	8.8 x 43.8 x 30.5
Unit Weight (lbs.)	13.5
Unit Weight (kg)	6.12
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.