

## Internet Office 120V 700VA 425W Standby UPS, USB port, 6 Outlets, Tel/DSL/Ethernet Protection

MODEL NUMBER: INTERNETOFFICE700



### Description

Tripp Lite's INTERNETOFFICE700 standby UPS system offers surge suppression and long-lasting battery support for personal computers, internetworking equipment and other sensitive electronics. Internal UPS circuits support entry-level PC systems for up to 45 minutes during power failures and brownouts so that connected equipment can be shut down without data loss. Offers complete desktop power protection in an attractive gray tower configuration. Includes 3 battery-supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. HID-compliant USB port enables optional unattended system shutdown without data loss in the case of extended power failure; USB cable included. HID compliant USB port enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. PowerAlert software available via FREE download. Built-in RJ45 TEL/Ethernet suppression jacks protect modem, fax machine, cordless phone or other peripheral with a standard single-line tel/DSL or data line connection. Built-in audible alarm and 3 front panel LEDs indicate line power status, battery power status and battery low/replace status. 700VA/425W power handling ability supports entry-level PCs, network workstations, point-of-sale equipment, small business phone systems, audio/video equipment and home theater systems. Offers 3.9 min. battery runtime with a full load of 700VA and 11.2 min. with a half load of 350VA. Supports user battery replacement via built-in access panel. \$150,000 connected equipment insurance (USA and Canada Only).

### Features

- INTERNETOFFICE700 standby UPS system offers UPS battery support, plus complete AC and tel/Ethernet line surge suppression
- Supports entry-level PC systems for up to 45 min. during brownouts and power failures to enable a safe system shutdown
- Supports a max load of 700VA/425W for 3.9 min.

### Highlights

- 700VA tower 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- USB port, TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

### Package Includes

- INTERNETOFFICE700 UPS System
- USB cable
- Phone cable
- Instruction manual



- Supports a half load of 350VA/215W for 11.2 min.
- Supplies battery-derived AC output during brownouts starting at 99V, user adjustment allows fine tuning of brownout response to any setting from 83V to 99V
- Attractive gray tower configuration
- Includes 3 battery-supported outlets plus 3 additional surge suppression-only outlets, and 6-ft. AC line cord (all NEMA 5-15)
- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert)
- HID-compliant USB port enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically restarting them, and rebooting completely locked computers by automatically switching UPS power off and back on again
- Built-in phone/Ethernet suppression jacks protect modem, fax machine or other peripheral with a dialup,DSL, or data line connection
- Built-in audible alarm and 3 front panel LEDs indicate line power, battery power and battery low/replace status
- 700VA/425W power handling ability supports a variety of computer, internetworking, telecom and consumer electronics equipment
- Supports hot-swap battery replacement via built-in access panel
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Compatible with 120V/60Hz applications for USA, Canada, Mexico and more
- \$150,000 connected equipment insurance (USA and Canada Only)

## Specifications

OVERVIEW	
UPC Code	037332033284
UPS Type	Standby
OUTPUT	
Output Volt Amp Capacity (VA)	700
Output Watt Capacity (Watts)	425
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	+/- 5%



UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(6) 5-15R
Individually Controllable Load Banks	No
<b>INPUT</b>	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P; Right-Angled
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
<b>BATTERY</b>	
Full Load Runtime (min.)	3.9 min. (425w)
Half Load Runtime (min.)	11.2 min. (215w)
DC System Voltage (VDC)	12
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//www.tripplite.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS~RBC51">RBC51</a>&nbsp;
Battery Access	Battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
Expandable Runtime	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	3 LEDs indicate line power, battery power and battery low/replace status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	510



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
AC Suppression Response Time	Instantaneous
Dataline Suppression	1 line TEL / DSL or 10Base T Ethernet protection
<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (UPSWM - tower mounting kit)
Primary Form Factor	Tower
Primary UPS Depth (mm)	191
Primary UPS Height (mm)	274
Primary UPS Width (mm)	132
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 34.80
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 13.70
Shipping Weight (kg)	7.30
Shipping Weight (lbs.)	16.10
UPS Housing Material	PVC
UPS Power Module Dimensions (hwd, cm)	27.43 x 13.21 x 19.05
UPS Power Module Dimensions (hwd, in.)	10.8 x 5.2 x 7.5
UPS Power Module Weight (kg)	6.89
UPS Power Module Weight (lbs.)	15.2
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	24
AC Mode Efficiency Rating (100% Load)	99%
<b>COMMUNICATIONS</b>	
Communications Interface	USB (HID enabled)
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at <a href="http://www.tripplite.com/poweralert">http://www.tripplite.com/poweralert</a>



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at <a href="http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp+Lite">http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite</a>
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	99 (adjustable to 83 via back panel potentiometer)
High Voltage Transfer to Battery Power (Setpoint)	139
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 &nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a> &nbsp;

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>