

Isobar 4-Outlet Surge Protector, 6-ft. Cord, 3300 Joules, Tel/Fax/Modem Suppression

MODEL NUMBER: ISOTEL



Highlights

- 4 outlets/6-ft. cord
- 3330 joule rating
- All metal housing with LED's
- Isolated filter banks
- Modem/fax surge protection
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Package Includes

- ISOTEL Surge Suppressor
- RJ11 telephone cable
- Instruction manual with warranty information

Description

For more than 20 years, America's leading companies have trusted Tripp Lite's Isobar Premium surge and noise suppressors to protect sensitive computer, networking and telecom equipment. With more than 18 million satisfied customers, the Isobar remains the world's #1 selling premium surge suppressor. Loaded with a generous combination of high quality components, near indestructible all-metal case, unique noise filtration system and built-in single line phone suppression for modems, the Isobar/Isotel series offers the highest level of protection attainable in a multi-outlet strip. Robust surge suppression circuits with sine-wave tracking offer extreme levels of protection against the heaviest surge conditions exceeding IEEE 587 category A & B specifications and reducing 6,000V test surges to harmless levels under 35 volts. Isobar's unique protection system combines large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors into exclusive isolated filter banks that remove EMI/RFI interference, even noise generated by other pieces of connected equipment. ISOTEL offers 4 outlets arranged in two filter banks to prevent system crashes, reboots and performance problems common as noisy system peripherals are powered off and on. Surge suppression rated at 3330 joules/92,000 amps offers network-grade protection. Widely spaced NEMA 5-15 outlets accommodate up to 4 large transformer plugs without blocking outlets. Pair of RJ11 jacks offer single phone line surge suppression for modems, fax machines and cordless phones. Includes 6 foot AC line cord with space-saving angled input plug and keyhole mounting tabs.

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 4 NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz (Requires NEMA 5-15R wall receptacle)

SUPPRESSION: AC: 140V RMS Clamping/3330 joules/92,000 amps PHONE: Single line protection starts at 260V

Features

- Tripp Lite's ISOBAR/ISOTEL is the world's #1 selling premium suppressor series with more than 18 million satisfied customers and a safety-tested history of 20+ years
- Robust surge suppression with sine-wave tracking protects against the heaviest of surge conditions, exceeding IEEE category A&B specifications and reducing 6,000V test surges to harmless levels less



Powering Business Worldwide



than 35 volts

- Multi-component suppression circuits combine toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors into exclusive isolated filter banks that remove EMI/RFI interference, even noise from other pieces of connected equipment
- Single phone line surge suppression protects modems, fax machines and cordless phones (2 wire, single line, RJ11 jacks)
- 4 outlets arranged in two filter banks prevent system crashes, reboots and performance problems common as noisy peripherals are powered off and on
- Network grade surge suppression rated at 3330 joules/92,000 amps
- Widely spaced outlets accommodate up to 4 large transformer plugs without blocking outlets
- Lighted power switch with integrated 12 amp circuit breaker offers power control and overload protection
- 6 foot AC line cord with space-saving angled input plug
- Keyhole mounting tabs for installation on a variety of applications
- 120V AC, 50/60Hz electrical compatibility
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- UL1449 listed - surge suppression (330V let-through), UL1283 listed - EMI protection, UL1363 listed - power tap, UL497A listed - communications suppression, cUL approved to Canadian standards, Complies with part 68 - FCC rules

Specifications

OVERVIEW	
UPC Code	037332010223
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Maximum Surge Amps	135000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1440
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	12
Transformer Accommodation	(2) Yes

Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and two position red illuminated on/off power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3330
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
AC Suppression Surge Current Rating	92,000 amps (36,000 NM / 56,000 CM)
AC Suppression Components Used	Metal oxide varistors, toroidal balanced chokes, ferrite rod-core inductors and VHF capacitors.
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended over-voltages and catastrophic occurrences
UL1449 Let Through Rating	330V - UL Verified
IEEE587 Cat. A Ringwave Let-Through	Less than 35 volts
EMI / RFI Filtering	40-80 dB
Isolated Filter Banks	2
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Color	Light Gray
Material of Construction	Metal
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	131.90mm
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 39.45mm; Distance between vertical outlets = 38.89mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	11.40 x 2.75 x 7.10



Powering Business Worldwide



Shipping Dimensions (hwd / cm)	28.96 x 6.98 x 18.03
Shipping Weight (lbs.)	2.70
Shipping Weight (kg)	1.22
Unit Dimensions (hwd / in.)	2.500 x 6.000 x 3.500
Unit Dimensions (hwd / cm)	6.4 x 15.2 x 8.9
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.