



Powering Business Worldwide

# 1200VA 1200W Line Conditioner - Automatic voltage regulation with surge protection

MODEL NUMBER: LC1200WM

## Description

Tripp Lite's wall-mountable LC1200WM automatic voltage regulation system offers complete protection from brownouts, overvoltages and transient surges for computers, printers, telecommunications systems and more. Transformer-based voltage correction circuits maintain usable 120V nominal AC output during brownouts as low as 87V and overvoltages to 140V. Network grade equipment protection offers AC surge and noise suppression. Supports heavy loads up to 1200 watts. Rugged, all-metal case with keyhole mounting tabs allow secure 4-screw mounting on walls and other surfaces. Includes 4 NEMA5-15R outlets, 6-ft. line cord and lighted power switch. \$25,000 Ultimate Lifetime Insurance (USA & Canada Only).

## Features

- Maintains usable 120V nominal output during brownouts as low as 87V and overvoltages as high as 140V
- 1200 watts output power rating supports heavy 120V loads up to 10 amps
- All-metal case with keyhole mounting tabs for secure 4-screw mounting on walls and other surfaces
- Network grade surge suppression
- Complete EMI/RFI noise filtering
- Lighted red switch indicates power status
- 4 protected NEMA5-15R outlets
- 6-ft. AC power cord with standard NEMA5-15P input plug
- 2 year manufacturers product warranty
- \$25,000 Ultimate Lifetime connected equipment insurance (USA & Canada Only)

## Highlights

- Automatically adjusts low or high voltage
- 1200 watts continuous
- 4 NEMA 5-15R outlets
- Wallmount cabinet keeps unit conveniently out of the way
- \$25,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

## Package Includes

- LC1200WM Line Conditioner
- Mounting hardware
- Instruction manual

## Specifications

OVERVIEW	
UPC Code	037332040299
INPUT	
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	
Output (Watts)	1200
Output Receptacles	(4) 5-15R
Output Nominal Voltage	120V / 60Hz
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	Lighted power switch shows incoming power status
SURGE / NOISE SUPPRESSION	



Powering Business Worldwide

UPS AC Suppression Joule Rating	1200
EMI / RFI AC Noise Suppression	80 dB
<b>PHYSICAL</b>	
Material of Construction	Steel
Form Factors Supported	Short tower format with keyhole slots for wall-mount applications
Shipping Dimensions (hwd / in.)	8.00 x 7.25 x 10.00
Shipping Dimensions (hwd / cm)	20.32 x 18.42 x 25.40
Shipping Weight (lbs.)	11.80
Shipping Weight (kg)	5.35
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	12.7 x 12.7 x 18.42
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.