

## USB-A to Lightning Sync/Charge Cable, MFi Certified - White, M/M, USB 2.0, 3 ft. (0.91 m)

MODEL NUMBER: M100-003-WH



This USB Type-A to Lightning cable connects your iPhone, iPad or iPod device to the USB port on your computer or wall/car charger

### Features

Tripp Lite's M100-003-WH 3-ft. (0.91 m) White USB Sync / Charge Cable with Lightning connector allows for uploading and downloading data, while charging the devices at the same time. Cable is MFi-certified for use with the latest generation of iPhone, iPad and iPod devices. Reversible Lightning connector allows plug-ability in either direction to the device.

### Highlights

- Features a reversible 8-pin Lightning plug and a USB-A plug
- Works with any computer
- MFi-certified for broad compatibility with your Apple iPhone, iPad or iPod
- Compatible with all devices with 8-pin connectors
- Plugs into Apple device in either direction

### Applications

- Charge and sync your Apple iPhone, iPad or iPod using the USB-A port on your computer or a wall charger up to 3-ft. (0.91 m) away
- Transfer photos and other important files between an external hard drive and your Apple device

### System Requirements

- Device or charger with USB-A port
- Most current iPhone, iPad and iPod devices

### Package Includes

- M100-003-WH USB Sync/Charge Cable with Apple Lightning Connector

## Specifications

OVERVIEW	
UPC Code	037332182173
Technology	Lightning; USB; USB 2.0 (High Speed)
USB Cable Type	Passive
INPUT	
Maximum Input Amps	2
POWER	
USB Power Delivery (PD) Charging Support	No

<b>CHARGING</b>	
Total Charging Watts	12
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	2.8mm
Wire Gauge (AWG)	30/24
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	4.57 x 2.36 x 0.05
Shipping Dimensions (hwd / cm)	11.61 x 5.99 x 0.13
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
Unit Packaging Type	Box
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	12W (5V/2.4A)
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	LIGHTNING (MALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
Data Transfer Rate	480 Mbps
USB Specification	USB 2.0 (up to 480 Mbps)
Angled Plug	No

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

STANDARDS & COMPLIANCE	
Product Certifications	MFi
Product Compliance	RoHS; REACH; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

# TRIPP-LITE

by **EAT•N**

© 2022 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.