

## Heavy-Duty USB Sync/Charge Cable with Lightning Connector, 6 ft. (1.8 m)

MODEL NUMBER: M100-006-HD



Heavy-duty Lightning cable charges and synchronizes your latest-generation Apple iPhone, iPad or iPod using the USB port on your computer. Constructed using bulletproof Aramid fiber, this cable is built to provide maximum performance under the most rigorous circumstances

### Description

The M100-006-HD Heavy-Duty USB Sync/Charge Cable connects your latest-generation iPhone, iPad or iPod to the USB-A port on a computer or USB wall charger, so you can charge your Apple device and transfer data. The reversible 8-pin Lightning plug connects in either direction to ensure fast, easy connection every time. Constructed using bulletproof Aramid fiber to reinforce the conductors inside the cable, this heavy-duty Lightning cable features enhanced protection to stand up to the most rigorous use. The double braided nylon jacket and integral strain relief provide additional strength and flexibility to endure the stress and abuse of frequent use.

The six-foot (1.8-meter) heavy-duty Lightning cable is MFi-certified for use with iPhone, iPad and iPod devices. It's compatible with iPhone (5, 5c, 5s, 6, 6 Plus, 6s, 6s Plus, SE, 7, 7 Plus, 8, 8 Plus, X, XR, XS, XS Max), iPad (4th, 5th and 6th generations), iPad mini, iPad mini 2, iPad mini 3, iPad mini 4, iPad Air, iPad Air 2, iPod Touch (5th and 6th generations), iPad Pro 12.9 inch (1st and 2nd generations), iPad Pro 10.5 inch and iPad Pro 9.7 inch.

### Features

**Syncs and Charges Your Apple 8-Pin Electronic Devices** Connects to USB-A port on computer or wall charger Supports optimal charging of 5V 2.4A (12W) MFi-certified for use with iPhone, iPad and iPod devices Compatible with iPhone (5, 5c, 5s, 6, 6 Plus, 6s, 6s Plus, SE, 7, 7 Plus, 8, 8 Plus, X, XR, XS, XS Max), iPad (4th, 5th and 6th generations), iPad mini, iPad mini 2, iPad mini 3, iPad mini 4, iPad Air, iPad Air 2, iPod Touch (5th and 6th generations), iPad Pro 12.9 inch (1st and 2nd generations), iPad Pro 10.5 inch and iPad Pro 9.7 inch

**Reversible Lightning Connector** Fumble-free reversible Lightning plug connects in either direction for quick connection every time

**Heavy-Duty Construction with Bulletproof Aramid Fiber** Constructed using bulletproof Aramid fiber, this cable stands up to rigorous and frequent use Double braided nylon jacket helps maintain top performance and long life Integral strain relief helps cable and connectors move freely without stress or cracking

## Specifications

### Highlights

- Constructed using bulletproof Aramid fiber, this cable stands up to rigorous and frequent use
- Connects to USB-A port on computer or wall charger
- MFi-certified for use with iPhone, iPad and iPod devices
- Nylon braiding maintains top performance and long life
- Reversible Lightning plug connects in either direction

### System Requirements

- USB-equipped computer or charger
- iPhone (5, 5c, 5s, 6, 6 Plus, 6s, 6s Plus, SE, 7, 7 Plus, 8, 8 Plus, X, XR, XS, XS Max), iPad (4th, 5th and 6th generations), iPad mini, iPad mini 2, iPad mini 3, iPad mini 4, iPad Air, iPad Air 2, iPod Touch (5th and 6th generations), iPad Pro 12.9 inch (1st and 2nd generations), iPad Pro 10.5 inch and iPad Pro 9.7 inch

### Package Includes

- M100-006-HD Heavy-Duty USB Sync/Charge Cable with Lightning Connector, 6 ft.



<b>OVERVIEW</b>	
UPC Code	037332207319
<b>INPUT</b>	
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
<b>PHYSICAL</b>	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.2mm
Color	Black; White
Material of Construction	PU, Nylon
Shipping Dimensions (hwd / cm)	2.31 x 6.10 x 13.72
Shipping Dimensions (hwd / in.)	0.91 x 2.40 x 5.40
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
Unit Packaging Type	Box
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Relative Humidity	0% to 90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	LIGHTNING (MALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
Technology	Lightning; USB
<b>CERTIFICATIONS</b>	
Certifications	Tested to RoHS, CA65, REACH; MFI-Certified



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>