

## Safe-IT Universal USB-A to Lightning, USB Micro-B and USB-C Sync/Charge Antibacterial Cable (M/3xM), MFi Certified, White, 4 ft. (1.2 m)

MODEL NUMBER: M101AB-004-LMCW



All-in-one cable with antibacterial properties connects your Apple, Android and Bluetooth mobile devices to the USB-A port on your computer or wall/car charger.

### Features

#### All-in-One USB Cable Charges and Syncs Your Frequently Used Mobile Devices

Now you can charge and synchronize all your devices with a single cable and avoid the tangle and clutter of multiple cords. This Safe-IT™ sync/charge cable (M/3xM) features Apple Lightning, USB Micro-B and USB-C connectors on the same end, which allows you to connect almost any mobile device to your computer, laptop or wall charger's USB-A port. Not only does the M101AB-004-LMCW charge and power your device, it simultaneously syncs and transfers photos, MP3s and other important files at USB 2.0 data transfer speeds up to 480 Mbps. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

#### Antibacterial Properties Provide Extra Protection

The molded connectors and PVC jacket are constructed using an antibacterial material that is effective in inhibiting the growth of Escherichia coli (E. coli) and Staphylococcus aureus (staph). This added protection makes this cable an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

#### Single Cable Solution Offers Flexibility in Meeting Your Syncing and Charging Needs

Ideal for home, office or travel use, this versatile cable is compatible with most smartphones, tablets, digital cameras, Bluetooth headphones and power banks, including your Android LG, Google or Samsung Galaxy phone or Surface Pro tablet. The 20V 3A (60W) USB-C connector is MFi-certified for safe use with the latest generation of iPhone, iPod and iPad devices.

#### Reversible Connectors Attach in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C and 8-pin Lightning connectors plug into a compatible port in either direction for an instant connection every time.

## Specifications

### OVERVIEW

### Highlights

- Single charge/sync cable for all your devices cuts down on clutter – carry just one!
- Made with antibacterial material proven effective in inhibiting the growth of E. coli and staph
- MFi-certified for broad compatibility with your Apple iPhone, iPad or iPod
- Supports USB 2.0 speeds up to 480 Mbps to ensure reliable charging and data transfers
- Reversible Lightning and USB-C plugs connect in either direction for immediate use

### Applications

- Charge and sync your iPhone, iPad, Android smartphone, tablet or other device using the USB port on your computer or a wall charger up to 4 ft. away
- Transfer photos and other important files between an external hard drive and your mobile device
- Provide extra protection against bacteria to give cable installers and IT personnel peace of mind during installation

### System Requirements

- Computer, laptop or charger with USB-A port
- Mobile device with Lightning, USB Micro-B or USB-C port
- Most current iPhone, iPad and iPod devices

### Package Includes

M101AB-004-LMCW Universal USB-A to Lightning, USB Micro-B and USB-C Sync/Charge Antibacterial Cable (M/3xM), White, 4 ft. (1.2 m)

UPC Code	037332261090
Technology	Lightning; USB 2.0 (High Speed)
Cable Type	Passive
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.7mm
Cable Length (ft.)	4
Cable Length (m)	1.22
Cable Length (in.)	48
Shipping Dimensions (hwd / in.)	0.95 x 2.50 x 4.80
Shipping Weight (kg)	0.07
Unit Packaging Type	Box
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	Micro-B: 2.5W (5V/0.5A); USB-A: 12W (5V/2.4A); USB-C: 60W (20V/3A)
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	LIGHTNING (MALE)
Side B - Connector 2	USB C (MALE)
Side B - Connector 3	MICRO-USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
USB Specification	USB 2.0 (up to 480 Mbps)

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Antibacterial	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	MFi
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.