

## USB Sync/Charge Cable with Apple 30-Pin Dock Connector, White, 3 ft. (1 m)

MODEL NUMBER: **M110-003-WH**



Charge and sync your Apple 30-pin iPhone, iPad or iPod using the USB port on your computer.

### Description

The M110-003-WH USB Sync/Charge Cable connects your iPhone, iPad or iPod with the USB port on any computer, so you can charge your Apple device and transfer data. This 3-foot cable is MFi-certified for use with iPhone, iPad and iPod devices. It's compatible with iPhone (4s, 4, 3Gs, 3G and iPhone), iPad (3rd generation), iPad 2, iPad, iPod Touch (1st through 4th generation), iPod classic and iPod nano (1st through 6th generation).

### Features

#### Syncs and Charges Your Apple 30-Pin Electronic Devices

- MFi-certified for use with iPhone, iPad and iPod devices
- Compatible with iPhone (4s, 4, 3Gs, 3G and iPhone), iPad (3rd generation), iPad 2, iPad, iPod Touch (1st through 4th generation), iPod classic and iPod nano (1st through 6th generation)

#### Compact and Convenient to Use

- Connects your 30-pin iPhone, iPad or iPod device and the USB port on your computer or wall charger
- Works with all computers

## Specifications

OVERVIEW	
UPC Code	037332190062
INPUT	

### Highlights

- Features an Apple-compatible 30-pin plug and a USB-A plug
- Works with any computer
- MFi-certified for use with iPhone, iPad and iPod devices
- Compatible with all Apple devices with 30-pin connectors

### System Requirements

- USB-equipped computer or charger
- iPhone (4s, 4, 3Gs, 3G and iPhone), iPad (3rd generation), iPad 2, iPad, iPod Touch (1st through 4th generation), iPod classic and iPod nano (1st through 6th generation)

### Package Includes

- M110-003-WH USB Sync/Charge Cable with Apple 30-Pin Dock Connector



Cable Length (ft.)	3
Cable Length (m)	1
<b>PHYSICAL</b>	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	2.8mm
Color	White
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	13.21 x 2.29 x 6.60
Shipping Dimensions (hwd / in.)	5.20 x 0.90 x 2.60
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
Unit Packaging Type	Box
Wire Gauge (AWG)	24 Power Pair / 30 Data Pair
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Relative Humidity	0% to 90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	30 PIN APPLE (MALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
Technology	Apple® 30-Pin Dock; USB
<b>CERTIFICATIONS</b>	
Certifications	Tested to MFI, CA65, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>