EdgeReady Micro Data Center



Compact Floor-Standing, 21U Usable, 3 kVA, 230V

Benefits

- Provides preconfigured IT infrastructure for edge computing servers, storage and network hardware in space-limited locations
- Integrates secure rack space, reliable power distribution, expandable battery backup, remote management and passive cooling
- Prevents configuration errors, reduces installation time, decreases field costs and standardizes edge computing infrastructure
- Ships three business days from receipt of order, after design, assembly and testing by experts in a controlled environment

Included Hardware


- A SR24UB Compact Rack Enclosure (Standard Width)
- B SMX3000XLRT2UA SmartPro® UPS System with P052-008 Input Cord and WEBCARDLX Network Management Card
- **E2MTHDI** Environmental Sensor (Temperature/Humidity/Digital Inputs)
- **D PDUMH20HV** Metered PDU

Specifications

Warranty³

Also includes (21) 1U blanking panels with toolless mounting. Assembled/tested unit includes reinforced shock pallet and loading ramps for stable shipment and reshipment with installed IT equipment. Kit version includes major components ready for final assembly on-site.

See Next Page for Customization Options



Model (Kit)	MDK2F21UPX00000
Model (Assembled/Tested)	MDA2F21UPX00000
Output Power Capacity	3 kVA/2.7 kW/11.7A Max
Rack Space	24U Total; 21U Usable
Weight Capacity	453 kg Total; 363 kg Usable
Maximum Device Depth	826 mm
Site Power Requirements	230V, 13/16A, 50/60 Hz
Site Outlet Required	BS 1363 (Standard) or CEE 7/7 "Schuko" (Optional)
UPS Type	Line-Interactive with Sine Wave Output
Runtime (50%/100% Load)	11/3.9 min. (Expandable)
High-Availability Features	Automatic Voltage Regulation (AVR);
	Battery Backup; Hot-Swappable Batteries
Usable Outlets (UPS + PDU)	(16) C13, (2) C19
Dimensions (Assembled)	1158 x 600 x 851 mm
Weight (Assembled)	91 kg

2-Year Limited Warranty (Extendable)

*Any component with a warranty longer than 2 years will be covered by the longer warranty.



Powering and Connecting Your World

Unlimited Micro Data Center Customization

Tripp Lite's solutions team is standing by to help you tailor your EdgeReady micro data center to match the business and technology requirements of your edge deployment strategy. We ship custom solutions in as little as five business days, assembled and tested. We can help you customize your EdgeReady micro data center in several ways:

- · Quick and easy customization via add-on accessories for the stock configurations
- Upgrades to included components of stock configurations with ready-to-ship alternatives
- · Customization of individual components like racks, PDUs and cables (increases lead time)



B020-U16-19-IP 1U Rack Console with 16-Port KVM Switch and Remote Access



SRXCOOL12KBPortable Air Conditioning Unit
(3.5 kW)



B093-008-2E4U-M 8-Port Console Server with Built-in Modem for Fail-Safe Access



PDUMH20HVNET 1U Switched PDU with Remote Current Monitoring, Alerts and Outlet Control

Switched PDU	PDUMH20HVNET with (8) C13; 1U (Replaces standard PDU.)
Battery Packs for Extended Runtime (50%/100% Load)	30/11 min. with BP48V24-2U (Limit 1); 43/16 min. with BP48V27-2US; 67/26 min. with BP48V60RT-3U
Cooling	SRXCOOL12KB (3.5 kW; Portable; BS 1363) or SRXCOOL12K (3.5 kW; Portable; CEE 7/7 "Schuko")
KVM Switch	B022-U16-IP; B020-U16-19-IP (With LCD Console)
Console Server	B093-008-2E4U-M
Door Monitoring Kit	SRSWITCH (Monitors front/rear doors.)
Airflow Management	SR1UBRUSH
Cable Managers	40+ Horizontal, Vertical and External Cable Management Options at tripplite.com
Power Cords	French/German UPS Input Cord with CEE 7/7 "Schuko" Plug (P050-008); Match Others to IT Equipment; 250+ Power Cord Options at tripplite.com
Network Cables	Match to IT Equipment; 1000+ Copper and Fiber Network Cable Options at tripplite.com
Patch Panels	60+ Copper and Fiber Patch Panel Options at tripplite.com
Additional Sensors	E2MT (Connect up to 3 sensors total per WEBCARDLX to monitor top/middle/bottom temperature.)

1111 W. 35th Street, Chicago, IL 60609 USA $\,\mid\,\,$ +1.773.869.1212 $\,\mid\,\,$ tripplite.com

