

Universal Swivel Monitor Stand/Riser

MODEL NUMBER: MR1815SWVL



Raises your monitor 6 in. above your desk, table or workspace's surface and swivels 360°. Ideal for monitors and televisions up to 50 in. and 88 lb.

Description

The MR1815SWVL Universal Swivel Monitor Stand not only frees up valuable space on your desk, table or workstation, it does so with chic, contemporary style that fits perfectly into any home or office décor. It rotates 360 degrees and features two extra-large wooden shelves measuring 18 x 15.25 inches. One shelf fits six inches above the other, allowing plenty of storage space between them for documents, paper clips, pens and other office necessities.

By holding your monitor six inches above the surface, the MR1815SWVL helps ease eye and neck strain. It supports up to 88 pounds, making it ideal for monitors and televisions up to 50 inches, as well as laptops, printers and fax machines. Sturdy metal legs with a rubber swivel wheel beneath secures the riser on smooth surfaces. The MR1815SWVL assembles in seconds using the included hardware.

Features

Raises a Monitor 6 in. Above Your Desk's Surface

- Swivels 360°
- Frees up valuable work space
- Helps ease strain on eyes and neck
- For home or office
- Allows room for storage
- Ideal for monitors and televisions up to 50 in.

Durable Construction

- Extra-large 18 x 15.25 in. wooden shelves support up to 88 lb.
- Sturdy metal legs with rubber swivel wheel secures riser on smooth surfaces

Highlights

- Extra-large 18 x 15.25 in. wooden shelves
- Sturdy metal legs with rubber swivel wheel
- Allows room underneath for keyboard storage
- Supports up to 88 lb.
- Assembles easily in seconds

Package Includes

- Top shelf
- Bottom shelf
- (4) Metal legs
- (4) Finishing screws
- (4) Long screws
- Assembly instructions



- Assembles easily in seconds using included hardware
- Contemporary easy-cleaning design fits any home or office décor

Specifications

OVERVIEW	
UPC Code	037332202536
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Degrees of Motion	360 Swivel
Material of Construction	Wood, Steel
Maximum Weight Capacity (kg)	40
Maximum Weight Capacity (lbs.)	88
Mounting Location	Desktop
Shipping Dimensions (hwd / cm)	8.99 x 52.50 x 45.49
Shipping Dimensions (hwd / in.)	3.54 x 20.67 x 17.91
Shipping Weight (kg)	5.19
Shipping Weight (lbs.)	11.44
Unit Dimensions (hwd / cm)	17.5 x 45.9 x 38.9
Unit Dimensions (hwd / in.)	6.9 x 18.1 x 15.3
Unit Weight (kg)	4.58
Unit Weight (lbs.)	10.10
FEATURES & SPECIFICATIONS	
Tools Necessary	No
SPECIAL FEATURES	
Cord Management	No
STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH and CE
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>