

Monitor Riser for Desk - Wood Top, USB-A Charge and Data Ports

MODEL NUMBER: MR229USB



Computer monitor stand lifts your monitor 3.1 in. above your workstation surface to help ease eye and neck strain.

Features

Maintenance-Free Computer Monitor Stand Raises Your Screen for Comfortable Viewing

This desk monitor riser allows you some flexibility in placing your monitor for maximum comfort. The legs raise your laptop or monitor 3.1 inches (80 millimeters) above the surface of your desk, so you can view your screen while lessening strain on your eyes and neck. Lifting your monitor also frees up valuable space on your desk, table or counter at home, school or office.

Rugged Wood and Metal Construction Supports Up to 44 Pounds

The wood platform measures 21.8 x 8.5 inches (554 x 215 millimeters) and supports monitors, laptops, printers, small televisions and other devices weighing up to 44 pounds (20 kilograms). A keyboard fits beneath it when not in use to clear up useful space on your desktop.

USB Ports Keep Essential Workplace Accessories Ready

One Quick Charge port and two USB-A ports allow powering and charging of phones and tablets. An LED indicator shows you that your connected devices are receiving power. A USB cable and AC power supply are included.

Sets Up Quickly and Easily in Just a Few Seconds

This monitor stand riser requires no assembly and is ready to use right out of the box. The legs are designed to prevent slipping on a level surface.

Highlights

- Computer riser lifts your monitor or laptop 3.1 in. above your workspace
- Eases eye and neck strain while clearing valuable space on your desk or table
- Quick Charge and USB ports allow charging of smartphones and tablets
- LED indicator lets you know at a glance connected devices are receiving power
- Rectangular wood platform supports monitor or other devices up to 44 lb.

Package Includes

- MR229USB Monitor Riser
- USB cable
- AC power adapter
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332283900
Device Compatibility	Monitor/HDTV
INPUT	



Powering Business Worldwide



AC Power Adapter Input Specs (V / Hz / A)	100-240v, 50/60Hz; 85A
AC Power Adapter Output Specs (V / A)	12Vdc 2.0 Adapter
PHYSICAL	
Color	White
Material of Construction	Plastic, Steel, MDF, Wood
Mounting Location	Desktop
Maximum Weight Capacity (lbs.)	44
Maximum Weight Capacity (kg)	20
Number of Displays	1
Shipping Dimensions (hwd / in.)	21.80 x 12.40 x 42.30
Shipping Dimensions (hwd / cm)	55.37 x 31.50 x 107.44
Shipping Weight (lbs.)	4.90
Shipping Weight (kg)	2.22
Unit Dimensions (hwd / in.)	3.150 x 21.800 x 8.460
Unit Dimensions (hwd / cm)	8 x 55.4 x 21.5
Unit Weight (lbs.)	4.96
Unit Weight (kg)	2.25
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	No
Security Lock	No
Height Adjustable	No
Outdoor Use	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS; RoHS3
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.