

Thunderbolt 3 Dock, Dual Display - 4K 60 Hz, UHD, HDMI, DisplayPort, USB 3.2 Gen 1, USB-A Hub, GbE

MODEL NUMBER: MTB3-DOCK-01



Thunderbolt 3 dock adds HDMI, DisplayPort, USB-A and Ethernet ports to your MacBook, EliteBook or other Thunderbolt 3 device.

Features

Thunderbolt 3 Docking Station Turns Your MacBook or Other Notebook into a Workstation This Thunderbolt 3 dock expands the potential of your MacBook or EliteBook's Thunderbolt 3 port. It's ideal for transmitting digital 4K audio and video to two large displays simultaneously, adding a thumb drive or other USB peripheral and connecting to a Gigabit Ethernet network—all at the same time.

Supports DisplayPort Alternate Mode for Transmitting Audio/Video Signals By connecting the built-in Thunderbolt 3 cable to a source device that supports DisplayPort Alt Mode, you can output 4K video and digital audio to a compatible monitor, television or projector without installing special software drivers.

Thunderbolt 3 Supports Blisteringly Fast 40 Gbps Data Transfer Speeds The Thunderbolt 3 cable supports bidirectional data transfer rates up to a sizzling 40 Gbps, which is eight times faster than USB 3.0, four times faster than Thunderbolt 1 and twice as fast as Thunderbolt 2. With dual 20 Gbps channels moving data both directions at the same time, the MTB3-DOCK-01 is perfectly suited for 4K video streaming and editing on two monitors, as well as transferring large RAW video or CAD files.

DisplayPort Multi-Stream Transport (MST) Allows Connection of Multiple Displays By connecting the included Thunderbolt 3 cable to a source that supports DisplayPort MST Mode, you may connect two displays simultaneously. This allows you to display the same 4K image on both monitors, extend your host desktop across both with different windows open on each, or combine both into one large display as a 4K video wall.

Transmits True 4K Video and Digital Audio The HDMI and DisplayPort outputs support true 4K resolutions up to 4K x 2K (4096 x 2160) at 60 Hz. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications.

USB Port Connects Keyboards, Thumb Drives and Other USB Peripherals The USB-A hub port accepts USB peripherals, such as flash drives, mice, keyboards and printers. It supports fast USB 3.2 Gen 1 data transfer rates up to 5 Gbps (10 times faster than USB 2.0) and is backward compatible with USB 2.0 and USB 1.1 devices.

Accesses a Wired Gigabit Ethernet Network The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Reversible Thunderbolt 3 Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible Thunderbolt 3 male connector plugs into its port in either direction for an instant connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play Thunderbolt 3 dock is specifically designed for use with the MacBook Pro and other notebook computers equipped with a Thunderbolt 3 port. It requires no software or external power source. It's about the size of

Highlights

- Connects two 4K displays at the same time for multitasking and increasing productivity
- Supports true 4K UHD resolutions up to 4096 x 2160 (@ 60 Hz) for crystal-clear video
- Joins a wired 10/100/1000 Gigabit Ethernet network when no Wi-Fi is available
- Supports Thunderbolt 3 speeds up to 40 Gbps between compatible devices
- USB-A data ports allow connection of flash drives and other peripherals

Applications

- Extend or mirror your MacBook or EliteBook on multiple displays to aid in multitasking and increase productivity
- Transfer data from one Thunderbolt 3 device to another at 40 Gbps
- Access a wired Gigabit Ethernet network in a location with no or spotty Wi-Fi
- Connect a USB microphone/headset to record a podcast or listen to music

System Requirements

- Source device with Thunderbolt 3 port that supports USB DisplayPort Alternate Mode and DisplayPort MST Mode (see owner's manual for details)
- Display device(s) with HDMI or



a smartphone, making it easy to pack into a pocket, backpack or laptop bag for multiport convenience wherever you go.

DisplayPort input*
*Both HDMI and DisplayPort outputs can transmit 4K video simultaneously. See owner's manual for details.

Package Includes

- MTB3-DOCK-01 Thunderbolt 3 Dock, Dual Display, Black
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332241986
Product Type	Docking Station
Technology	Cat6; DisplayPort; HDMI; Thunderbolt; USB; USB 3.1 (Gen 1)
Host Connector	THUNDERBOLT 3 (Type-C MALE)
VIDEO	
Number of Monitors Supported	2
Video Ports	DISPLAYPORT (FEMALE); HDMI (FEMALE)
Video Ports Details	DisplayPort 1.2; HDMI 2.0; HDCP 2.2
Resolutions Supported	DisplayPort: 4K 60Hz (4096 x 2160)HDMI: 4K 60Hz (4096 x 2160)
Max Supported Video Resolution	4096 x 2160 (4K x 2K) @ 60 Hz (Both DP and HDMI)
Extended Mode	Yes
Extended Mode Details	1x DP (4K 60Hz) + 1x HDMI (4K 60Hz)
Mirror Mode	Yes
Mirror Mode Details	1x DP (4K 60Hz) + 1x HDMI (4K 60Hz)
Max Supported Color Depth	36-bit Deep Color
Chroma Sub Sampling	4:4:4
DATA	
Data Ports	(1) USB A (FEMALE)
Data Ports Details	(1) USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)



INPUT	
Built-In Cable Length (ft.)	0.79
Built-In Cable Length (m)	0.24
Built-In Cable Length (in.)	9.45
Built-In Cable Length (cm)	24
Bus Powered	Yes
POWER	
USB Power Delivery (PD) Charging Support	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power), Orange (Transmitting Data)
CHARGING	
Total Charging Watts	0
PHYSICAL	
Color	Black
Material of Construction	Polycarbonate, ABS, TPE
Unit Dimensions (hwd / cm)	2 x 5.6 x 10.5
Unit Dimensions (hwd / in.)	1.0 x 4.13 x 2.24
Unit Packaging Type	Box
Unit Weight (kg)	0.07
Unit Weight (lbs.)	0.154
ENVIRONMENTAL	
Operating Temperature Range	32 ~ 104F (0 ~ 40C)
Storage Temperature Range	-4 ~ 185F (-20 ~ 85C)
Power Consumption (Watts)	13.5
Operating Humidity Range	10% RH ~ 85% RH (No Condensation)
Storage Humidity Range	5% RH ~ 90% RH (Non Condensation)
COMMUNICATIONS	
Network Speed	Gigabit Ethernet (10/100/1000)
IEEE Standards Supported	802.3
CONNECTIONS	



Ports	4
Dock Connectors	DISPLAYPORT, HDMI, USB-A RJ45 LAN
Side A - Connector 1	THUNDERBOLT 3 (Type-C FEMALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
Side B - Connector 2	USB A (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
Side B - Connector 4	RJ45 (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2
USB Hub Ports	Yes
Number of USB Hub Ports	1
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>