

2-Port European-Style Insert, Unloaded Shuttered Angled Module, Icon Tabs, White, TAA

MODEL NUMBER: N042E-WM2-SAT



European-style insert accepts compatible keystone jacks for terminating premise audio/video, voice or data applications.

Features

European Insert Connects Your In-Wall Audio/Video, Voice or Data Cable Application

This European-style insert with unloaded shuttered angled module is ideal for your premise wiring applications, including home theater, VoIP phones and Ethernet. Just snap keystone jacks, including those used in HDMI, DisplayPort, RCA audio, USB and Cat5e/6/6a applications, into the cutouts for immediate cable connection. Compatible with N042E-WF1 gang frame, the angled module facilitates easy cable installation in tight spaces without excessive bending.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white module is shuttered to resist dust. It measures 45 x 45 millimeters and blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat. Use the icon tabs to quickly identify the connected ports.

Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- High-impact plastic construction designed to blend in with your home/office décor
- White insert measures 45 x 45 mm for a sleek, professional appearance
- Angled design allows easier installation in crowded spaces without damaging the cable

Package Includes

N042E-WM2-SAT 2-Port European-Style Insert, White

Specifications

OVERVIEW	
UPC Code	037332268921
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB 2.0 (High Speed)
Country/Region	Europe
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	(2) KEYSTONE JACK CUTOUT
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Color	White
Material of Construction	Spring: SUS304; All else: ABS (UL94V-0)
Total Number of Ports	2
Unit Dimensions (hwd / in.)	1.776 x 1.776 x 1.016
Finish	Matte
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.