

1-Port French-Style Wall Plate, White, TAA

MODEL NUMBER: **N042F-W01**



French-style wall cover plate accepts a compatible keystone jack for terminating premise audio/video, voice or data applications.

Features

French Wall Plate Connects Your In-Wall Audio/Video, Voice or Data Cable Line

This French-style wall cover plate is ideal for your premise wiring applications, including home theater, VoIP phones and Ethernet. Just snap a keystone jack, including one used in HDMI, DisplayPort, RCA audio, USB and Cat5e/6/6a applications, into the plate's cutout for immediate cable connection.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white cover plate measures 81 x 81 millimeters and blends elegantly into any home or office décor for a sleek, professional installation. Mounting screws are included for wall installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

TAA-Compliant for GSA Schedule Purchases

The N042F-W01 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement

Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- High-impact plastic construction designed to last long in your décor
- White outer frame measures 81 x 81 mm for a sleek, professional appearance
- Hardware included for mounting with compatible keystone jack (sold separately)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- N042F-W01 1-Port French-Style Wall Plate, White
- (2) Mounting screws

Specifications

OVERVIEW	
UPC Code	037332268945
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB
Country/Region	France
PHYSICAL	
Color	White
Material of Construction	ABS

Total Number of Ports	1
Unit Dimensions (hwd / in.)	3.190 x 3.190 x 0.320
Unit Dimensions (hwd / mm)	81 x 81 x 8.10
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-40 to 154 F (-40 to 68 C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	KEYSTONE JACK CUTOUT
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty