

## Single-Gang French-Style Gang Frame, White, TAA

MODEL NUMBER: **N042F-WF1**



French-style gang frame accepts compatible wall-mount insert for terminating premise audio/video, voice or data applications.

### Features

#### French Gang Frame Connects Your In-Wall Audio/Video, Voice or Data Cable Line

This gang frame for mounting or trunking is ideal for terminating your premise wiring applications, including home theater, VoIP phones and Ethernet. The French-style N042F-WF1 protects electrical and network cables to help prevent accidental damage to your application. It's compatible with Tripp Lite's N042E-WM1-S unloaded shuttered module and N042E-WHM0 blank insert (sold separately).

#### High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white plastic cover plate measures 80 x 85 millimeters (outer frame) and fits one 45 x 45 millimeter insert module. It helps hide unattractive cabling and blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

#### TAA-Compliant for GSA Schedule Purchases

The N042F-WF1 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

### Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- Helps prevent accidental cable damage and hides unattractive wiring
- Compatible with select Tripp Lite N042E-Series modules and inserts (sold separately)
- High-impact plastic construction designed to blend in with your home/office décor
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

N042F-WF1 Single-Gang French-Style Gang Frame, White

## Specifications

OVERVIEW	
UPC Code	037332268952
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB
Country/Region	France
PHYSICAL	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Color	White
Material of Construction	ABS
Total Number of Ports	1
Unit Dimensions (hwd / in.)	OUTER: 3.37 x 3.15 x 0.78; INNER: 1.77 X 1.77
Unit Dimensions (hwd / mm)	OUTER: 85.6 x 80 x 20; INNER: 45 X 45
Finish	Matte
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 TO 140 F (-10 to 60 C)
Storage Temperature Range	-40 TO 154.4 F (-40 to 68 C)
Operating Humidity Range	10% TO 90% RH, (NON-CONDENSING)
Storage Humidity Range	10% TO 90% RH, (NON-CONDENSING)
<b>CONNECTIONS</b>	
Number of Ports	1
Side A - Connector 1	KEYSTONE JACK CUTOUT
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS; REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>