

Triple-Gang French-Style Gang Frame, White, TAA

MODEL NUMBER: N042F-WF3



French-style gang frame accepts compatible wall-mount inserts for terminating premise audio/video, voice or data applications.

Features

French Gang Frame Connects Your In-Wall Audio/Video, Voice or Data Cable Line

This gang frame for mounting or trunking is ideal for terminating your premise wiring applications, including home theater, VoIP phones and Ethernet. The French-style N042F-WF3 protects electrical and network cables to help prevent accidental damage to your application. It's compatible with Tripp Lite's N042E-WM1-S unloaded shuttered module and N042E-WHM0 blank insert (sold separately).

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white cover plate measures 80 x 175 millimeters (outer frame) and fits three 45 x 45 millimeter modules. It helps hide unattractive cabling and blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

TAA-Compliant for GSA Schedule Purchases

The N042F-WF3 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332268976
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB
Country/Region	France
PHYSICAL	

Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- Helps prevent accidental cable damage and hides unattractive wiring
- Compatible with select Tripp Lite N042E-Series modules and inserts (sold separately)
- High-impact plastic construction designed to blend in with your home/office décor
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

N042F-WF3 Triple-Gang French-Style Gang Frame, White, TAA

Color	White
Material of Construction	ABS
Total Number of Ports	0
Unit Dimensions (hwd / in.)	6.910 x 3.150 x 0.790
Unit Dimensions (hwd / mm)	OUTER: 175.5 x 80 x 20; INNER: 135 X 1.78
Finish	Matte
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-40 to 154 F (-40 to 68 C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty