

## 2-Port UK-Style Keystone Wall Plate, Unloaded Shuttered Module, White

MODEL NUMBER: N042U-W02-S



British-style wall cover plate accepts compatible keystone jacks for terminating premise audio/video, voice or data applications.

### Features

#### U.K. Keystone Wall Plate Connects Your In-Wall Audio/Video, Voice or Data Cable Line

This British-style cover plate with unloaded shuttered module is ideal for your premise wiring applications, including home theater, VoIP phones and Ethernet. Just snap a keystone jack, including one used in HDMI, DisplayPort, RCA audio, USB and Cat5e/6/6a applications, into the plate's cutouts for immediate cable connection. The wall plate is compatible with Tripp Lite's N042U-MB1 single-gang surface mounting box.

#### High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white module is shuttered to resist dust. It measures 86 x 86 millimeters and blends elegantly into any home or office décor for a sleek, professional installation. Mounting screws are included for wall installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat. Ports can be labeled for quick identification at a glance.

## Specifications

OVERVIEW	
UPC Code	037332269447
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB
Country/Region	UK
PHYSICAL	
Color	White
Material of Construction	Spring: Stainless Steel; Faceplate: ABS

### Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- Compatible with any style of keystone jack, including HDMI, USB and Cat5e/6
- High-impact plastic construction designed to blend in with your home/office décor
- White outer frame measures 86 x 86 mm for a sleek, professional appearance

### Package Includes

- N042U-W02-S 2-Port UK-Style Keystone Wall Plate, White
- (2) Mounting screws

Total Number of Ports	2
Unit Dimensions (hwd / in.)	3.390 x 3.390 x 0.420
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-40 to 154 F (-40 to 68 C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
<b>CONNECTIONS</b>	
Number of Ports	2
Side A - Connector 1	(2) KEYSTONE JACK CUTOUT
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty