

Single-Gang UK-Style Gang Frame for Insert Modules, Hidden Screws, White

MODEL NUMBER: N042U-WF1-1



British-style gang frame accepts compatible wall-mount insert for terminating premise audio/video, voice or data applications.

Features

U.K. Gang Frame Connects Your In-Wall Audio/Video, Voice or Data Cable Line

This gang frame for unloaded insert modules is ideal for terminating your premise wiring applications, including home theater, VoIP phones and Ethernet. The UK-style N042U-WF1-1 also protects electrical and network cables to help prevent accidental damage to your application. It's compatible with Tripp Lite's N042U-Series unloaded shuttered modules and inserts (sold separately).

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white plastic cover plate measures 86 x 86 millimeters (outer frame) and accepts one 50 x 50 millimeter module. The screw holes are hidden behind the front of the gang frame to help it blend elegantly into any home or office décor for a sleek, professional installation. Just remove the front clip from the gang frame to mount it using the included hardware. The ABS plastic construction meets UL 94HB flame-retardant standards for protection against fire and high heat.

Specifications

OVERVIEW	
UPC Code	037332269461
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB
Country/Region	UK
PHYSICAL	
Color	White
Material of Construction	ABS, AS

Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- Helps prevent accidental cable damage and hides unattractive wiring
- Compatible with select Tripp Lite N042U-Series modules and inserts (sold separately)
- High-impact plastic construction designed to blend in with your home/office décor

Package Includes

N042U-WF1-1 Single-Gang UK-Style Gang Frame, White

Total Number of Ports	1
Unit Dimensions (hwd / in.)	3.380 x 3.380 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-40 to 154 F (-40 to 68 C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	KEYSTONE JACK CUTOUT
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty