

## Double-Gang UK-Style Gang Frame for Insert Modules, White, TAA

MODEL NUMBER: N042U-WF2-2



British-style gang frame accepts compatible wall-mount inserts for terminating premise audio/video, voice or data applications.

### Features

#### U.K. Gang Frame Connects Your In-Wall Audio/Video, Voice or Data Cable Line

This gang frame for unloaded insert modules is ideal for terminating your premise wiring applications, including home theater, VoIP phones and Ethernet. The UK-style N042U-WF2-2 also protects electrical and network cables to help prevent accidental damage to your application. It's compatible with N042U-Series unloaded shuttered modules and inserts (sold separately).

#### High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white plastic cover plate measures 86 x 146 millimeters (outer frame) and accepts either four 25 x 50 millimeter modules or eight 12.5 x 50 millimeter modules. It blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

### Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- Helps prevent accidental cable damage and hides unattractive wiring
- Compatible with select N042U-Series modules and inserts (sold separately)
- High-impact plastic construction designed to blend in with your home/office décor

### Package Includes

N042U-WF2-2 Double-Gang UK-Style Gang Frame, White

## Specifications

OVERVIEW	
UPC Code	037332269485
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB
Country/Region	UK
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	KEYSTONE JACK CUTOUT
PHYSICAL	



Powering Business Worldwide

TRIPP LITE  
SERIES

Color	White
Material of Construction	ABS
Total Number of Ports	1
Unit Dimensions (hwd / in.)	9.060 x 7.090 x 0.500
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.