

4-Port UK-Style Gang Frame for 6C-Type Insert Module, White

MODEL NUMBER: N042U-WF2-6C



British-style gang frame accepts up to 4 compatible 6C-type modules for terminating premise data (Ethernet) applications.

Features

U.K. Gang Frame Connects Your In-Wall Data Cable Line

This gang frame for 6C-type insert modules is ideal for terminating your data communications wiring application, including Gigabit Ethernet. The UK-style N042U-WF2-6C also protects electrical and network cables to help prevent accidental damage to your application.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white gang frame measures 86 x 146 millimeters (outer frame) and accepts up to four 25 x 38.5 millimeter 6C-type insert modules. It blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

Specifications

OVERVIEW	
UPC Code	037332269553
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a
Country/Region	UK
PHYSICAL	
Color	White
Material of Construction	ABS
Total Number of Ports	4

Highlights

- Ideal for completing a data (Ethernet) in-wall wiring installation
- Helps prevent accidental cable damage and hides unattractive wiring
- High-impact plastic construction designed to blend in with your home/office décor

Package Includes

N042U-WF2-6C 4-Port UK-Style Gang Frame, White

Unit Dimensions (hwd / in.)	5.750 x 3.390 x 0.590
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	(4) KEYSTONE JACK CUTOUT
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty