

1-Port UK-Style Insert, Unloaded Shuttered Module, 25 x 50 mm, White

MODEL NUMBER: N042U-WHM-S



Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- Compatible with any style of keystone jack, including HDMI, USB and Cat5e/6
- High-impact plastic construction designed to blend in with your home/office décor
- White insert measures 25 x 50 mm for a sleek, professional appearance

Package Includes

N042U-WHM-S 1-Port UK-Style Insert, White

British-style module mounts within a compatible wall plate for terminating premise audio/video, voice or data applications.

Features

UK Shuttered Module Connects Your Audio/Video, Voice or Data Network

This UK-style insert with unloaded shuttered module is ideal for your premise wiring applications, including home theater, VoIP phones and Ethernet. Just snap a keystone jack, including one used in HDMI, DisplayPort, RCA audio, USB and Cat5e/6/6a applications, into the module's cutout for immediate cable connection.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white module is shuttered to resist dust. It measures 25 x 50 millimeters and blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat. The insert is compatible with Tripp Lite's N042U-WF1-1, N042U-WF1-2 and N042U-WF2-2 gang frames.

Specifications

OVERVIEW	
UPC Code	037332269508
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB 2.0 (High Speed)
Country/Region	UK
PHYSICAL	
Color	White
Material of Construction	Spring: Stainless Steel; Faceplate: ABS
Total Number of Ports	1

Unit Dimensions (hwd / in.)	1.970 x 0.970 x 0.340
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-40 to 154 F (-40 to 68 C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	KEYSTONE JACK CUTOUT
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty