

1-Port UK-Style Unloaded Shuttered Module, 50 x 50 mm, White

MODEL NUMBER: **N042U-WM1-S**



British-style shuttered module mounts within a compatible gang frame for terminating premise audio/video, voice or data applications.

Features

U.K. Shuttered Module Connects Your Audio/Video, Voice or Data Network

This British-style unloaded shuttered module is ideal for your premise wiring applications, including home theater, VoIP phones and Ethernet. Just snap a keystone jack, including one used in HDMI, DisplayPort, RCA audio, USB and Cat5e/6/6a applications, into the module's cutout for immediate cable connection. The insert is compatible with N042U-WF1-1, N042U-WF1-2 and N042U-WF2-2 gang frames.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white module is shuttered to resist dust. It measures 50 x 50 millimeters and blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- Compatible with any style of keystone jack, including HDMI, USB and Cat5e/6
- High-impact plastic construction designed to blend in with your home/office décor
- Shuttered to prevent dust and other debris from damaging cable connection

Package Includes

N042U-WM1-S 1-Port UK-Style Unloaded Shuttered Module, White

Specifications

OVERVIEW	
UPC Code	037332269492
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB 2.0 (High Speed)
Country/Region	UK
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	KEYSTONE JACK CUTOUT
PHYSICAL	
Color	White



Powering Business Worldwide



Material of Construction	Spring: Stainless Steel; Faceplate: ABS
Total Number of Ports	1
Unit Dimensions (hwd / in.)	1.960 x 1.960 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
FEATURES & SPECIFICATIONS	
Antibacterial	No
Snagless Connector	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.