

# Network Cable Continuity Tester for Cat5/Cat6, Phone and Coax Cable Assemblies

MODEL NUMBER: **N044-000-R**



## Highlights

- Combines main tester unit and removable remote tester unit
- Identifies mis-wires, short circuits and open circuits
- Includes coax converters and terminator for BNC and F coaxial cables
- Vinyl storage pouch protects units from damage in crowded toolbox

## Package Includes

- Main tester
- Remote tester
- (2) BNC/F coax adapters
- Coax terminator
- Storage pouch

Tests Cat5e, Cat6, telephone and coaxial cable connections with the press of a button.

## Features

### Essential Tool for Cable Installers or Telecom/LAN Personnel

The N044-000-R allows you to test wiring continuity for Cat5, Cat6, telephone and coax cable assemblies at the press of a button. A combination of main tester unit and removable remote tester unit, the N044-000-R identifies crossed wires, short circuits and open circuits in BNC, F, RJ11, RJ12 and RJ45 cables. When not in use, the two-piece set can be stored in its vinyl carrying case to protect it from being damaged inside a crowded toolbox. Requires one 9V battery (not included) to operate.

## Specifications

| OVERVIEW                        |   |
|---------------------------------|---|
| UPC Code                        | 037332138743                                    |
| Accessory Type                  | Cable Tester                                    |
| Technology                      | Cat5/5e; Cat6; Cat6a                            |
| Accessory Class                 | Audio Video Accessories; Networking Accessories |
| CONNECTIONS                     |   |
| Side A - Connector 1            | RJ45 (FEMALE)                                   |
| Side B - Connector 1            | RJ11 (FEMALE)                                   |
| PHYSICAL                        |   |
| Color                           | Beige; Black                                    |
| Shipping Dimensions (hwd / in.) | 2.20 x 6.70 x 5.70                              |
| Shipping Dimensions (hwd / cm)  | 5.59 x 17.02 x 14.48                            |



Powering Business Worldwide



|                                     |                           |
|-------------------------------------|---------------------------|
| Shipping Weight (lbs.)              | 0.56                      |
| Shipping Weight (kg)                | 0.25                      |
| Unit Dimensions (hwd / in.)         | 0.000 x 0.000 x 0.000     |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Product Compliance                  | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>       |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.