

48-Port 2U Rack-Mount Cat5e 110 Patch Panel, 568B, RJ45 Ethernet, TAA

MODEL NUMBER: N052-048



Highlights

- 19-in. rackmount ready, 2U Height (3.50in)
- EIA/TIA 2/32 spacing
- 110 type punchdown termination
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Cat5e Patch Panel 568B-48 Port, 2U

Description

Enhanced Cat5 Patch Panels offer you all the functionality and compatibility as any name brand. Each panel comes with 110-type termination, while meeting and exceeding EIA/TIA TSB-40 Cat5e connecting hardware specifications. Color-coded for both EIA/TIA 568A and 568B installations. 48 ports ensure a wide range of plug-n-play options. The clear numbering on both the front and back of each panel gives you a quick and easy way to identify cable runs, and the high-density 19-inch panel design will save you valuable space in on the rack.

UTP Cat5e 22-24 AWG solid cable

Features

- Cat5e
- UL approved
- Ports clearly numbered both on front and back
- Labels on front enable each port to be named
- Color coded label on back offers both EIA/TIA 568A & 568B wiring
- Metal frame
- EIA/TIA 2/32 spacing
- Rack mountable on a 19 rack (2U Height, 3.50in)

Specifications

OVERVIEW	
UPC Code	037332013200
Product Type	Punchdown
Technology	Cat5/5e

PHYSICAL	
Shipping Dimensions (hwd / in.)	2.80 x 19.70 x 4.70
Shipping Dimensions (hwd / cm)	7.11 x 50.04 x 11.94
Shipping Weight (lbs.)	2.30
Shipping Weight (kg)	1.04
CONNECTIONS	
Number of Ports	48
Side A - Connector 1	110 IDC
Side B - Connector 1	RJ45 (FEMALE)
PoE Type	Type 2 PoE+ (30W, IEEE 802.3at)
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty