

24-Port 1U Rack-Mount 110-Type Color-Coded Patch Panel, RJ45 Ethernet, 568B, Cat5/5e

MODEL NUMBER: N053-024-RBGY



Manages and organizes up to 24 input and output Cat5/5e network cable connections in just 1U of an EIA-standard 19 in. rack. Recommended for Ethernet, Fast Ethernet and Gigabit Ethernet network applications.

Description

The UL-approved N053-024-RBGY 24-Port 1U Rack-Mount 110-Type Color-Coded Patch Panel manages and organizes up to 24 input and output UTP Cat5/5e network cable connections in just 1U of an EIA-standard 19 in. rack.

The 24 RJ45 ports are split into four banks of six ports each that are color-coded—red, blue, green and yellow—for easily identifiable zones. Rear 110 connections are also color-coded for convenient EIA/TIA 568A/B wiring. All ports are numbered front and rear for quick identification of connections.

Recommended for Ethernet, Fast Ethernet and Gigabit Ethernet network applications, this durable metal patch panel complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. It supports 22 to 26 AWG stranded and solid wire.

Features

Manages and Organizes 24 UTP Cat5/5e Network Connections

- Recommended for Ethernet, Fast Ethernet and Gigabit Ethernet network applications
- Ports split into 4 color-coded banks of 6 ports each for convenient zone cabling
- Color-coded 110 connections for EIA/TIA 568A/B wiring
- Ports numbered front and rear for easy ID of cable runs
- Supports 22 to 26 AWG stranded and solid wire

Reliable Construction and Easy Installation

Highlights

- 4 color-coded banks for convenient zone cabling
- Color-coded rear 110 connections for EIA/TIA 568A/B wiring
- Supports 22 to 26 AWG stranded and solid wire
- Ports numbered front and rear for easy ID of cable runs
- Mounts into 1U of EIA-standard 19 in. rack

Package Includes

- N053-024-RBGY 24-Port 1U Rack-Mount 110-Type Color-Coded Patch Panel
- Mounting hardware
- Quick Start Guide



- Mounts easily into 1U of EIA-standard 19 in. rack
- UL-approved and RoHS-compliant
- Durable metal construction
- Meets or exceeds EIA/TIA TSB-40 Cat5e connecting hardware specifications

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

Specifications

OVERVIEW	
UPC Code	037332197467
PHYSICAL	
Shipping Dimensions (hwd / in.)	3.90 x 2.90 x 21.90
Shipping Dimensions (hwd / cm)	9.91 x 7.37 x 55.63
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
CONNECTIONS	
Ports	24
Side A - Connector 1	110 IDC
Side B - Connector 1	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	Cat5/5e
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>