

8-Port Keystone Double-Gang Faceplate, White, TAA

MODEL NUMBER: N080-208



Universal wall plate provides a clean and simple method for connecting audio/video, voice or Ethernet cable lines at the wall.

Features

Double-Gang Universal Keystone Wall Plate Connects up to 8 Cables The Tripp Lite N080-208 is ideal for connecting up to eight audio/video, voice and/or Ethernet cables at the wall. It's recommended for concrete walls and other locations where cables cannot be run through the wall. Any type of keystone jack, including Cat5e/6/6a, USB, HDMI, DisplayPort and RCA applications, snaps easily into the eight cutouts for quick cable connection.

Highly Adaptable to Match Your Specific Requirements The high-impact polycarbonate wall plate fits any mid-sized or standard double-gang box. It's colored white to blend elegantly into any home or office décor for a sleek, professional installation. Four mounting screws are included.

TAA-Compliant for GSA Schedule Purchases The N080-208 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332236289
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; USB 2.0 (High Speed); HDBaseT; HDMI; FireWire; DisplayPort
Country/Region	Global
PHYSICAL	
Color	White

Highlights

- Accommodates any keystone jack, including Cat5e/6/6a, USB, HDMI and DisplayPort
- High-impact polycarbonate construction designed to last a long time
- Classic white color blends elegantly into your home or office décor
- Hardware included for mounting to any mid-size or standard double-gang box
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Terminate up to 8 in-wall audio/video, voice and/or Ethernet cable lines simultaneously

Package Includes

- N080-208 8-Port Double-Gang Universal Keystone Wall Plate
- (4) #6-32 screws

Total Number of Ports	8
Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Shipping Dimensions (hwd / cm)	0.00 x 0.00 x 0.00
Shipping Weight (lbs.)	0.00
Shipping Weight (kg)	0.00
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Relative Humidity	10% to 90% RH
CONNECTIONS	
Number of Ports	8
Side A - Connector 1	KEYSTONE JACK CUTOUT
Side B - Connector 1	KEYSTONE JACK CUTOUT
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty