

## 8-Port Keystone Double-Gang Faceplate, White, TAA

MODEL NUMBER: **N080-208**



Universal wall plate provides a clean and simple method for connecting audio/video, voice or Ethernet cable lines at the wall.

### Features

**Double-Gang Universal Keystone Wall Plate Connects up to 8 Cables** The Tripp Lite N080-208 is ideal for connecting up to eight audio/video, voice and/or Ethernet cables at the wall. It's recommended for concrete walls and other locations where cables cannot be run through the wall. Any type of keystone jack, including Cat5e/6/6a, USB, HDMI, DisplayPort and RCA applications, snaps easily into the eight cutouts for quick cable connection.

**Highly Adaptable to Match Your Specific Requirements** The high-impact polycarbonate wall plate fits any mid-sized or standard double-gang box. It's colored white to blend elegantly into any home or office décor for a sleek, professional installation. Four mounting screws are included.

**TAA-Compliant for GSA Schedule Purchases** The N080-208 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

### Highlights

- Accommodates any keystone jack, including Cat5e/6/6a, USB, HDMI and DisplayPort
- High-impact polycarbonate construction designed to last a long time
- Classic white color blends elegantly into your home or office décor
- Hardware included for mounting to any mid-size or standard double-gang box
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Applications

- Terminate up to 8 in-wall audio/video, voice and/or Ethernet cable lines simultaneously

### Package Includes

- N080-208 8-Port Double-Gang Universal Keystone Wall Plate
- (4) #6-32 screws

## Specifications

| OVERVIEW                        |  |
|---------------------------------|--|
| UPC Code                        | 037332236289   |
| Technology                      | Cat5/5e; Cat6; Cat6a; USB 2.0 (High Speed); USB 3.0 (SuperSpeed); HDBaseT; HDMI; FireWire; DisplayPort |
| PHYSICAL                        |  |
| Color                           | White  |
| Shipping Dimensions (hwd / cm)  | 0.00 x 0.00 x 0.00   |
| Shipping Dimensions (hwd / in.) | 0.00 x 0.00 x 0.00   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                           |
|-------------------------------------|---------------------------|
| Shipping Weight (kg)                | 0.00                      |
| Shipping Weight (lbs.)              | 0.00                      |
| <b>ENVIRONMENTAL</b>                |                           |
| Operating Temperature Range         | 14 ~ 140F (-10 ~ 60C)     |
| Storage Temperature Range           | -40 ~ 154F (-40 ~ 68C)    |
| Relative Humidity                   | 10% ~ 90% RH              |
| <b>CONNECTIONS</b>                  |                           |
| Ports                               | 8                         |
| Side A - Connector 1                | KEYSTONE JACK CUTOUT      |
| Side B - Connector 1                | KEYSTONE JACK CUTOUT      |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>