

12-Port Keystone Double-Gang Faceplate, White, TAA

MODEL NUMBER: **N080-212**



Universal wall plate provides a clean and simple method for connecting audio/video, voice or Ethernet cable lines at the wall.

Features

Double-Gang Universal Keystone Wall Plate Connects up to 12 Cables The N080-212 is ideal for connecting up to 12 audio/video, voice and/or Ethernet cables at the wall. It's recommended for concrete walls and other locations where cables cannot be run through the wall. Any type of keystone jack, including Cat5e/6/6a, USB, HDMI, DisplayPort and RCA applications, snaps easily into the 12 cutouts for quick cable connection.

Highly Adaptable to Match Your Specific Requirements The high-impact polycarbonate wall plate fits any mid-sized or standard double-gang box. It's colored white to blend elegantly into any home or office décor for a sleek, professional installation. Four mounting screws are included.

TAA-Compliant for GSA Schedule Purchases The N080-212 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332236296
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; USB 2.0 (High Speed); HDBaseT; HDMI; FireWire; DisplayPort
Country/Region	Global
CONNECTIONS	
Number of Ports	12
Side A - Connector 1	KEYSTONE JACK CUTOUT

Highlights

- Accommodates any keystone jack, including Cat5e/6/6a, USB, HDMI and DisplayPort
- High-impact polycarbonate construction designed to last a long time
- Classic white color blends elegantly into your home or office décor
- Hardware included for mounting to any mid-size or standard double-gang box
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Terminate up to 12 in-wall audio/video, voice and/or Ethernet cable lines simultaneously

Package Includes

- N080-212 12-Port Double-Gang Universal Keystone Wall Plate
- (4) #6-32 screws



Powering Business Worldwide



Side B - Connector 1	KEYSTONE JACK CUTOUT
PHYSICAL	
Color	White
Total Number of Ports	12
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.15
Shipping Weight (kg)	0.07
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Relative Humidity	10% to 90% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.