

12-Port Keystone Double-Gang Faceplate, White, TAA

MODEL NUMBER: **N080-212**



Universal wall plate provides a clean and simple method for connecting audio/video, voice or Ethernet cable lines at the wall.

Features

Double-Gang Universal Keystone Wall Plate Connects up to 12 CablesThe Tripp Lite N080-212 is ideal for connecting up to 12 audio/video, voice and/or Ethernet cables at the wall. It's recommended for concrete walls and other locations where cables cannot be run through the wall. Any type of keystone jack, including Cat5e/6/6a, USB, HDMI, DisplayPort and RCA applications, snaps easily into the 12 cutouts for quick cable connection.

Highly Adaptable to Match Your Specific RequirementsThe high-impact polycarbonate wall plate fits any mid-sized or standard double-gang box. It's colored white to blend elegantly into any home or office décor for a sleek, professional installation. Four mounting screws are included.

TAA-Compliant for GSA Schedule PurchasesThe N080-212 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Accommodates any keystone jack, including Cat5e/6/6a, USB, HDMI and DisplayPort
- High-impact polycarbonate construction designed to last a long time
- Classic white color blends elegantly into your home or office décor
- Hardware included for mounting to any mid-size or standard double-gang box
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Terminate up to 12 in-wall audio/video, voice and/or Ethernet cable lines simultaneously

Package Includes

- N080-212 12-Port Double-Gang Universal Keystone Wall Plate
- (4) #6-32 screws

Specifications

OVERVIEW	
UPC Code	037332236296
Technology	Cat5/5e; Cat6; Cat6a; USB 2.0 (High Speed); USB 3.0 (SuperSpeed); HDBaseT; HDMI; FireWire; DisplayPort
PHYSICAL	
Color	White
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	0.07
Shipping Weight (lbs.)	0.15
ENVIRONMENTAL	
Operating Temperature Range	14 ~ 140F (-10 ~ 60C)
Storage Temperature Range	-40 ~ 154F (-40 ~ 68C)
Relative Humidity	10% ~ 90% RH
CONNECTIONS	
Ports	12
Side A - Connector 1	KEYSTONE JACK CUTOUT
Side B - Connector 1	KEYSTONE JACK CUTOUT
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>