

## Surface-Mount Box for Keystone Jack - 1 Port, White

MODEL NUMBER: **N082-001-WH**



Surface-mount box provides a single connection for non-premise home theater, VoIP or Ethernet cable applications on a wall or ceiling.

### Features

**Connects Audio/Video, Voice and Data Cable Lines in Your Network** This surface-mount box provides a fast, easy, cost-effective method for expanding your home theater (audio/video), VoIP phone (voice) or Ethernet (data) network. Any type of keystone jack, including those used in HDMI, DisplayPort, RCA, USB and Cat5e/6/6a applications, snaps easily into the cutout for quick cable connection.

**Easy to Install Where In-Wall Box and Wire Installation Is Impractical or Impossible** Just snap open the top cover to add the keystone jack, then snap the cover closed. Use zip ties to secure cabling to the box, which features a rear routing slot to allow the box to be installed flush against a wall, ceiling or baseboard. Mounting screws and double-sided tape are included. The flame-resistant ABS UL94V-0 box is white and blends elegantly into any home or office décor for a sleek, professional installation.

### Highlights

- Ideal for non-premise audio/video, voice or Ethernet data wiring installations
- Compatible with any type of keystone jack, including HDMI, Cat5/6, USB and DisplayPort
- Flame-resistant ABS UL94V-0 construction designed to last long in your décor
- Cabling routes through a rear shot to enable flush installation against a wall or ceiling
- Mounting hardware and double-sided tape included for installation practically anywhere

### Applications

- Complete your non-premise wiring application with a clean, sleek-looking appearance

### Package Includes

- N082-001-WH Surface-Mount Box, 1 Port, White
- (2) Mounting screws
- Double-sided tape
- Zip ties

## Specifications

OVERVIEW	
UPC Code	037332249623
Technology	Cat5/5e; Cat6
Country/Region	Global
PHYSICAL	
Color	White
Material of Construction	ABS
Total Number of Ports	1

<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 TO 140 F (-10 to 60 C)
Storage Temperature Range	-40 TO 154.4 F (-40 to 68 C)
Relative Humidity	10% TO 90% (NON-CONDENSING)
<b>CONNECTIONS</b>	
Number of Ports	1
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty