

## Surface-Mount Box for Keystone Jacks - 4 Ports, White

MODEL NUMBER: N082-004-WH



Surface-mount box provides 4 connections for non-premise home theater, VoIP or Ethernet cable applications on a wall or ceiling.

### Features

**Connects Audio/Video, Voice and Data Cable Lines in Your Network** This surface-mount box provides a fast, easy, cost-effective method for expanding your home theater (audio/video), VoIP phone (voice) or Ethernet (data) network. Any type of keystone jack, including those used in HDMI, DisplayPort, RCA, USB and Cat5e/6/6a applications, snaps easily into the cutout for quick cable connection.

**Easy to Install Where In-Wall Box and Wire Installation Is Impractical or Impossible** Just snap open the top cover to add the keystone jacks, then snap the cover closed. Use zip ties to secure cabling to the box, which features rear routing slots to allow the box to be installed flush against a wall, ceiling or baseboard. Mounting screws and double-sided tape are included. The flame-resistant ABS UL94V-0 box is white and blends elegantly into any home or office décor for a sleek, professional installation.

### Highlights

- Ideal for non-premise audio/video, voice or Ethernet data wiring installations
- Compatible with any type of keystone jack, including HDMI, Cat5/6, USB and DisplayPort
- Flame-resistant ABS UL94V-0 construction designed to last long in your décor
- Cabling routes through a rear slot to enable flush installation against a wall or ceiling
- Mounting hardware and double-sided tape included for installation practically anywhere

### Applications

- Complete your non-premise wiring application with a clean, sleek-looking appearance

### Package Includes

- N082-004-WH Surface-Mount Box, 4 Ports, White
- (2) Mounting screws
- Double-sided tape
- Zip ties

## Specifications

OVERVIEW	
UPC Code	037332249647
Technology	Cat5/5e; Cat6
PHYSICAL	
Material of Construction	ABS
Color	White
ENVIRONMENTAL	
Operating Temperature Range	14 TO 140 F (-10 to 60 C)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Storage Temperature Range	-40 TO 154.4 F (-40 to 68 C)
Relative Humidity	10% TO 90% (NON-CONDENSING)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>