

# Surface-Mount Box for Keystone Jacks - 12 Ports, White

MODEL NUMBER: N082-012-WH



Surface-mount box provides 12 keystone jack connections for non-premise home theater, VoIP or Ethernet cable applications on a wall or ceiling.

## Features

### Connects Audio/Video, Voice and Data Cable Lines in Your Network

This surface-mount box provides a fast, easy, cost-effective method for expanding your home theater (audio/video), VoIP phone (voice) or Ethernet (data) network. Any type of keystone jack, including those used in HDMI, DisplayPort, RCA, USB and Cat5e/6/6a applications, snaps easily into the cutout for quick cable connection. The N082-012-WH is also compatible with right-angle keystone jacks with the use of the included adapters.

### Easy to Install Where In-Wall Box and Wire Installation Is Impractical or Impossible

Just snap open the top cover to add up to 12 keystone jacks, then snap the cover closed. Use the included cable ties to secure cabling to the box. Vertical raceway slots at the top and bottom allow the box to be installed flush against a wall, ceiling or baseboard. Mounting screws are included.

### TAA-Compliant for GSA Schedule Purchases

The N082-012-WH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

## Specifications

OVERVIEW	
UPC Code	037332283399
Product Type	Surface Mount Box
Technology	Cat5/5e; Cat6; Cat6a; Cat8
Country/Region	Global
CONNECTIONS	
Number of Ports	12

## Highlights

Ideal for non-premise audio/video, voice or Ethernet data wiring installationsCompatible with any type of keystone jack, including HDMI, Cat5/6, USB and DisplayPortCabling routes through breakout raceways for easy ID and cable organizationCompatible with right-angle keystone jacks with use of included adaptersMounting hardware included for easy installation out of the box

## Package Includes

- N082-012-WH Surface-Mount Box, 12 Ports, White
- (8) Mounting screws
- (4) Cable ties
- (12) Keystone jack interface adapters
- Installation instructions



Powering Business Worldwide

**TRIPP-LITE**  
by **EATON**

PHYSICAL	
Color	White
Material of Construction	ABS
Mounting Location	Wall; Ceiling
Included Mounting Accessories	Y
Included Mounting Accessory Description	(4) Machine Screws; (4) Self Tapping Screws
Mounting Holes or Slots	Yes
Total Number of Ports	12
Unit Dimensions (hwd / in.)	1.290 x 5.510 x 6.690
Unit Dimensions (hwd / cm)	3.27 x 14 x 17
Unit Dimensions (hwd / mm)	32.7 x 140 x 170
Unit Packaging Type	Box
Mounting Details	Mounting screw holes compatible with single- and double-gang wall plates, 4 loops for cable tie fastening
Cable Entry/Exit	Breakouts on three sides for raceway/cable entry
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Relative Humidity	10% to 85% RH
FEATURES & SPECIFICATIONS	
Mounting Accessory Included	Yes
Antibacterial	No
Breakout	No
Numbered Ports	Yes
Driver Required	No
Recommended Category Cable	Cat6e, Cat6, Cat6a, Cat8, HDMI
Keystone Jacks	Yes
Panel Applications	Ethernet
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA C22.2 No. 182.4-M90 (Canada); UL 1863
Product Compliance	CE (Europe); REACH; RoHS; Trade Agreements Act (TAA); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.