

Cat3 25-Pair Telco Cable (RJ21 M/F), Gray, 25 ft. (7.62 m)

MODEL NUMBER: **N152-025-C3**



Highlights

- 25ft, 26AWG Cat3 UTP copper cable for extending voice connections.
- Use with Telephone, PBX, IP Phone Systems

System Requirements

- Communication equipment and connectivity devices utilizing 50pin Telco type connections.

Package Includes

- 1 - 25-ft. (7.62 m) Cat3 25-Pair Telco Cable, RJ21 M/F

Description

N152-Series Telco cables are ideal for telephone, PBX and IP Phone system applications. Constructed with 26 AWG solid conductor Cat3-rated cable and heavy-duty metal backshells with Male to Female, RJ21, 50-pin connectors. EIA/TIA 568B color-coded conductors. The N152 cable is only available in stock lengths of 25 feet (7.6 meters).

Features

- 25-ft. (7.62 m), 26AWG Cat3 UTP copper cable for extending voice connections
- Male to Female 50pin Centronics / Telco connectors
- Use with Telephone, PBX, and IP Phone Systems
- EIA/TIA 568B color code
- PVC Jacket
- Rugged metal backshell connectors
- RoHS Compliant

Specifications

OVERVIEW	
UPC Code	037332153418
Technology	Cat3
CONNECTIONS	
Side A - Connector 1	CENTRONICS 50 (MALE)
Side B - Connector 1	CENTRONICS 50 (FEMALE)
Crossover Wiring	No
Angled Connector	No



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Cable Jacket Color	Gray
Cable Shielding	UTP
Conductor Material	Solid Copper
Cable Length (ft.)	25
Cable Length (m)	7.62
Cable Length (in.)	300
Cable Length (cm)	762
Shipping Dimensions (hwd / in.)	14.20 x 11.00 x 0.50
Shipping Dimensions (hwd / cm)	36.07 x 27.94 x 1.27
Shipping Weight (lbs.)	2.00
Shipping Weight (kg)	0.91
COMMUNICATIONS	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	500 MHz
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Product Warranty Period (International)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.