

## Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), PoE, Blue, 3 ft. (0.91 m), 50-Piece Bulk Pack

MODEL NUMBER: N201-003-BL50BP



### Features

- 50 piece bulk pack of 3-ft. Blue Cat6 patch cables
- Meets Category 6 cabling standards
- Premium cabling for Category 6, Category 5e and Category 5 applications
- Length: 3-ft. / Color: Blue / Connectors: RJ45 male
- Drastically reduce impedance & structural return loss compared to standard 100MHz wire
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Deliver stable performance up to 550MHz/1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in other colors and lengths

### Highlights

- 50 piece bulk pack of 3-ft. Blue Cat6 patch cables
- Premium cabling for Category 6, Category 5e and Category 5 applications—rated for 550 MHz/1 Gbps communications
- Designed to meet Category 6 specifications; reduces cross-talk and return loss
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

### System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.

### Package Includes

- 50 pieces of 3-ft. Blue Cat6 Gigabit Snagless Molded Patch Cables

## Specifications

| OVERVIEW   |              |
|------------|--------------|
| UPC Code   | 037332176219 |
| Technology | Cat6         |
| PHYSICAL   |              |

|                                 |                                 |
|---------------------------------|---------------------------------|
| Cable Jacket Color              | Blue                            |
| Cable Jacket Material           | PVC                             |
| Cable Jacket Rating             | CM                              |
| Cable Shielding                 | UTP                             |
| Cable Outer Diameter (OD)       | 6.0 mm                          |
| Number of Conductors            | 4 Pair                          |
| Conductor Material              | Stranded Copper                 |
| Conductor Gauge                 | 24 AWG                          |
| Cable Length (ft.)              | 3                               |
| Cable Length (m)                | 0.91                            |
| Cable Length (in.)              | 36                              |
| Cable Length (cm)               | 91.4                            |
| Shipping Dimensions (hwd / in.) | 16.00 x 18.00 x 0.10            |
| Shipping Dimensions (hwd / cm)  | 40.64 x 45.72 x 0.25            |
| Shipping Weight (lbs.)          | 5.10                            |
| Shipping Weight (kg)            | 2.31                            |
| <b>ENVIRONMENTAL</b>            |                                 |
| Operating Temperature Range     | 14 to 122 F (-10 to 50 C)       |
| Storage Temperature Range       | 5 to 140 F (-15 to 60 C)        |
| Operating Humidity Range        | 0% to 90% RH, Non-Condensing    |
| Storage Humidity Range          | 0% to 90% RH, Non-Condensing    |
| <b>COMMUNICATIONS</b>           |                                 |
| Bandwidth per TIA Standard      | 250 MHz                         |
| Maximum Bandwidth as Tested     | 500 MHz                         |
| Network Compatibility           | 1 Gbps (Gigabit)                |
| IEEE Standards Supported        | 802.3an; 802.3at                |
| <b>CONNECTIONS</b>              |                                 |
| Side A - Connector 1            | RJ45 (MALE)                     |
| Side B - Connector 1            | RJ45 (MALE)                     |
| Crossover Wiring                | No                              |
| Contact Plating                 | Gold                            |
| PoE Type                        | Type 2 PoE+ (30W, IEEE 802.3at) |
| Connector Type                  | Snagless; Molded                |

|                                      |   |
|--------------------------------------|---|
| Wiring Configuration                 | EIA/TIA 568B  |
| Angled Connector                     | No  |
| <b>FEATURES &amp; SPECIFICATIONS</b> |   |
| IP68 Rated                           | No  |
| Snagless Connector                   | Yes   |
| Antibacterial                        | No  |
| IP20 Rated                           | No  |
| <b>STANDARDS &amp; COMPLIANCE</b>    |   |
| Product Certifications               | UL Listed; cUL Listed   |
| Product Compliance                   | CE (Europe); RoHS; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; UKCA |
| <b>WARRANTY &amp; SUPPORT</b>        |   |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty   |