



Powering Business Worldwide

14-ft. Blue Cat6 Gigabit Snagless Ethernet Cable

MODEL NUMBER: N201-014-BL-R



Description

With Tripp Lite's new category 6 molded patch cables you can stay ahead of the game by using this high-speed cable to distribute data, voice and video. These cables deliver stable performance up to 550MHz. Each comes UL verified meets EIA/TIA Cat6 TIA/EIA-568-B-2.1 draft 9 standards. Constructed with high-quality copper wire and a staggered-pin plug design, near-end crosstalk levels are kept to a minimum. Designed for use in category 6, category 5e and category 5 applications. Cat6 cables are available in a variety of colors with a snagless boot preventing cable snags. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. Clamshell retail packaging.

Features

- Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- Length: 14-ft. Color: blue Connectors: RJ45 male
- Drastically reduce impedance & structural return loss compared to standard 100MHz wire
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Deliver stable performance up to 550MHz/1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in other colors and lengths
- Warranted to be free from defects in materials and workmanship for life

Highlights

- Meets Category 6 cabling standards. Reduces return loss and cross talk
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801, and ETL (Category 6, draft 11)
- Drastically reduce impedance & structural return loss compared to standard 100Mhz wire
- Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation
- Feature molded connectors with integral strain relief. Rated for 550 MHz/1 Gbps communication. Comes in retail packaging
- Lifetime product warranty

System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.

Package Includes

- 14-ft. Cat6 Blue Gigabit Patch Cord Snagless Molded RJ45

Specifications

OVERVIEW	
UPC Code	037332116949



Powering Business Worldwide

CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Angled Connector	No
PHYSICAL	
Cable Jacket Color	Blue
Cable Shielding	UTP
Number of Conductors	4 Pair
Cable Length (ft.)	14
Cable Length (m)	4.27
Cable Length (in.)	168
Shipping Dimensions (hwd / in.)	7.00 x 7.00 x 2.25
Shipping Dimensions (hwd / cm)	17.78 x 17.78 x 5.72
Shipping Weight (lbs.)	0.66
Shipping Weight (kg)	0.30
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.