

Cat6 Gigabit Snagless Slim UTP Ethernet Cable (RJ45 M/M), Blue, 6 ft. (1.83 m)

MODEL NUMBER: N201-S06-BL



Connects network components like printers, computers, copiers, routers, servers, modems and switches. Ideal for high-density data centers. Slim design increases airflow in tight spaces.

Features

Perfect Solution for Your Networking Needs

- Ideal for connecting components like printers, computers, copiers, routers, servers, modems and switches in high-density data centers
- Designed for fast transmission and excellent signal quality
- Ensures peak performance throughout your LAN
- Delivers speeds up to Cat6 Gigabit/1 Gbps

Special Slim Design

- More than 38% smaller in diameter than standard Cat6 cable
- Increases airflow in tight spaces
- Extra flexible for installing around corners and through cable management panels

Premium Construction for Superior Performance

- Made from 28 AWG copper wire
- PVC 4-pair stranded UTP
- RJ45 male connectors
- Integral strain relief for long life

Snagless Connectors

- snagless boots prevent locking tabs from damage

Specifications

Highlights

- Over 38% slimmer than standard Cat6 cables
- Rated for Cat6 Gigabit/1 Gbps communications
- Snagless RJ45 male connectors
- Easy to route through cable management panels
- High-quality 28 AWG copper wire

Package Includes

- N201-S06-BL Cat6 Gigabit Snagless Slim UTP Patch Cable (RJ45 M/M), 6 ft.



| OVERVIEW | |
|--------------------------------------|---------------------------|
| UPC Code | 037332193087 |
| Technology | Cat6 |
| PHYSICAL | |
| Color | Blue |
| Cable Jacket Rating | CM |
| Cable Shielding | UTP |
| Conductor Material | Stranded Copper |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Cable Length (in.) | 72 |
| Cable Length (cm) | 182.9 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Weight (kg) | 0.04 |
| Shipping Weight (lbs.) | 0.09 |
| COMMUNICATIONS | |
| Network Compatibility | 1 Gbps (Gigabit) |
| CONNECTIONS | |
| Side A - Connector 1 | RJ45 (MALE) |
| Side B - Connector 1 | RJ45 (MALE) |
| Connector Type | Molded; Snagless |
| FEATURES & SPECIFICATIONS | |
| Snagless Connector | Yes |
| STANDARDS & COMPLIANCE | |
| Certifications | RoHS Compliant |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>