

## Left-Angle Cat6 Gigabit Molded UTP Ethernet Cable (RJ45 Left-Angle M to RJ45 M), Blue, 3 ft. (0.91 m)

MODEL NUMBER: N204-003-BL-LA



### Highlights

- Space saving design
- Left Angle connector to Straight
- Cat6 Gigabit rated

### System Requirements

- Use with Cat6, Cat5e, Cat5, or VoIP networks

### Package Includes

3-ft. (0.91 m) Blue Cat6 Left Angle to Straight RJ45 - RJ45 Patch cable

### Features

- 3-ft. (0.91 m) Blue Cat6, Left Angle to Straight RJ45 - RJ45 Patch cable
- PVC 4 Pair Stranded Conductors, 24AWG
- Fully Molded Ends
- ETL Verified to TIA/EIA -568-B
- 550Mhz Gigabit Speed Rated

## Specifications

OVERVIEW	
UPC Code	037332167514
Technology	Cat6
PHYSICAL	
Color	Blue
Cable Shielding	UTP
Cable Jacket Material	PVC
Cable Jacket Rating	CM
Number of Conductors	4 Pair
Conductor Material	Stranded Copper



Conductor Gauge	24 AWG
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Cable Length (cm)	91.4
Shipping Dimensions (hwd / cm)	0.25 x 14.99 x 22.86
Shipping Dimensions (hwd / in.)	0.10 x 5.90 x 9.00
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
<b>COMMUNICATIONS</b>	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	500 MHz
Maximum Data Rate	1Gbps
<b>CONNECTIONS</b>	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE) - LEFT ANGLE
Connector Type	Molded
Wiring Configuration	EIA/TIA 568B
<b>SPECIAL FEATURES</b>	
IP68 Rated	No
Snagless Connector	No
Antibacterial	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>