


Cat6 RJ45 Pass-Through UTP Modular Plug, 50 Pack, TAA

MODEL NUMBER: N232-050-UTP



Clear RJ45 Cat6 connectors terminate round solid or stranded conductor cabling in data and voice Ethernet applications.

Features

50 Pack of RJ45 Modular Plugs for Terminating Solid or Stranded Cat6 Cable

These RJ45 modular connectors make it easy to terminate solid or stranded conductor Cat6 cable in your data or voice Ethernet application. The RJ45 pass-through UTP (Unshielded Twisted Pair) plugs work with most RJ45 crimping tools (except AMP) and custom-length 24–26 AWG UTP Cat6 cabling at up to 6.2 mm jacket diameter. Conveniently packed in a rugged plastic bag that fits perfectly in your toolbox, these durable clear connectors feature 50-micron gold-plated contacts for optimal signal transmission and staggered nose patterns for minimal near-end crosstalk (NEXT).

Highlights

- 50 Cat6 RJ45 pass-through UTP modular plugs in an easy-to-pack plastic bag
- Work with most RJ45 crimping tools and 24-26 AWG UTP Cat6 cables
- 50 m gold-plated contacts promote premium data transfer
- Staggered nose pattern reduces near-end crosstalk for clearer transmission
- Ideal for use with solid or stranded conductor Cat6 cable in your Ethernet application

Applications

Terminate solid or stranded conductor cabling in Cat6 network applications

Package Includes

(50) Cat6 RJ45 pass-through UTP modular plugs

Specifications

OVERVIEW	
UPC Code	037332260697
Product Type	RJ45 Plug
Technology	Cat6; Cat6a
PHYSICAL	
Cable Shielding	UTP
Cable Outer Diameter (OD)	< 6.2 mm
Wire Gauge (AWG)	24 - 26
ENVIRONMENTAL	
Operating Temperature Range	-40° to 185°F (-40° to 85°C)
Storage Temperature Range	41° to 86°F (5° to 30°C)



Powering Business Worldwide



Relative Humidity	15% to 65% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.