

Cat6a Straight-Through Modular Shielded In-Line Snap-In Coupler with 90-Degree Down-Angled Port (RJ45 F/F), TAA

MODEL NUMBER: **N235-001-SH-6AD**



Fully shielded coupler with 90° angled port connects two Cat6a cables to provide feed-through patching with standard data wallplates. Ideal for premise wiring, telecommunications, data networking and Ethernet connections.

Description

Strengthen your high-speed network with the N235-001-SH-6AD Cat6a Straight-Through Modular Shielded In-Line Snap-In Coupler (F/F). It connects two Cat6a patch cords to create one longer cable. Its keystone design is perfect for convenient feed-through patching when used with a standard data wallplate (such as N042-001-WH). One RJ45 port is angled down at a 90-degree angle for easy installation in hard-to-reach spaces. Built for ultra-fast performance, this is an ideal coupler when setting up premise wiring, telecommunications, data networking and Ethernet connections.

Compatible with all Cat6a cables, the N235-001-SH-6AD's protective metal housing is fully shielded to reduce EMI/RFI interference that can damage or degrade data. This coupler features straight-through wiring and 50- μ m gold-plated contacts designed to resist corrosion. The N235-001-SH-6AD is UL-listed and meets all requirements for EIA/TIA Category 6A compliance. It's also backward compatible with Cat6, Cat5e and Cat5 LANs.

Features

Strengthens Your High-Speed Network

- Ideal for premise wiring, telecommunications, data networking and Ethernet connections
- Connects 2 Cat6a patch cables for a longer cable run
- Keystone design for easy snap-in installation in standard data wallplates (such as N042-001-WH)
- Compatible with all Cat6a cables
- Backward compatible with Cat6, Cat5e and Cat5 LANs

Superior Construction for Superior Performance

- 90° down-angled RJ45 port for easy installation in hard-to-reach spaces
- Fully shielded metal housing cuts down on EMI/RFI interference that can damage or degrade data
- 50- μ m gold-plated contacts resist corrosion and improve conduction
- Features straight-through wiring
- UL-listed

Highlights

- 90° down-angled RJ45 port for easy installation in tight spaces
- Protective shielded housing reduces EMI/RFI interference
- 50- μ m gold-plated contacts on RJ45 jacks
- Keystone design for use with standard data wallplate
- Backward compatible with Cat6, Cat5e and Cat5 LANs

Package Includes

- N235-001-SH-6AD Cat6a Straight-Through Modular Shielded In-Line Snap-In Coupler (RJ45 F/F)



Powering Business Worldwide



- Meets all EIA/TIA Category 6A requirements

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332197191
Product Type	RJ45 Coupler
Technology	Cat6a
CONNECTIONS	
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
PHYSICAL	
Color	Silver
Connector Color	Silver
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Relative Humidity	10% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.