

Cat6a Straight-Through Modular Shielded In-Line Snap-In Coupler with 90-Degree Down-Angled Port (RJ45 F/F), TAA

MODEL NUMBER: N235-001-SH-6AD



Fully shielded coupler with 90° angled port connects two Cat6a cables to provide feed-through patching with standard data wallplates. Ideal for premise wiring, telecommunications, data networking and Ethernet connections.

Description

Strengthen your high-speed network with Tripp Lite's N235-001-SH-6AD Cat6a Straight-Through Modular Shielded In-Line Snap-In Coupler (F/F). It connects two Cat6a patch cords to create one longer cable. Its keystone design is perfect for convenient feed-through patching when used with a standard data wallplate (such as Tripp Lite's N042-001-WH). One RJ45 port is angled down at a 90-degree angle for easy installation in hard-to-reach spaces. Built for ultra-fast performance, this is an ideal coupler when setting up premise wiring, telecommunications, data networking and Ethernet connections.

Compatible with all Cat6a cables, the N235-001-SH-6AD's protective metal housing is fully shielded to reduce EMI/RFI interference that can damage or degrade data. This coupler features straight-through wiring and 50- μ inch gold-plated contacts designed to resist corrosion. The N235-001-SH-6AD is UL-listed and meets all requirements for EIA/TIA Category 6A compliance. It's also backward compatible with Cat6, Cat5e and Cat5 LANs.

Features

Strengthens Your High-Speed Network

- Ideal for premise wiring, telecommunications, data networking and Ethernet connections
- Connects 2 Cat6a patch cables for a longer cable run
- Keystone design for easy snap-in installation in standard data wallplates (such as Tripp Lite's N042-001-WH)
- Compatible with all Cat6a cables
- Backward compatible with Cat6, Cat5e and Cat5 LANs

Superior Construction for Superior Performance

- 90° down-angled RJ45 port for easy installation in hard-to-reach spaces
- Fully shielded metal housing cuts down on EMI/RFI interference that can damage or degrade data
- 50- μ inch gold-plated contacts resist corrosion and improve conduction
- Features straight-through wiring

Highlights

- 90° down-angled RJ45 port for easy installation in tight spaces
- Protective shielded housing reduces EMI/RFI interference
- 50- μ inch gold-plated contacts on RJ45 jacks
- Keystone design for use with standard data wallplate
- Backward compatible with Cat6, Cat5e and Cat5 LANs

Package Includes

- N235-001-SH-6AD Cat6a Straight-Through Modular Shielded In-Line Snap-In Coupler (RJ45 F/F)



- UL-listed
- Meets all EIA/TIA Category 6A requirements

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332197191
Technology	Cat5/5e; Cat6; Cat6a
PHYSICAL	
Color	Silver
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Weight (kg)	0.02
Shipping Weight (lbs.)	0.04
ENVIRONMENTAL	
Operating Temperature Range	14 TO 140 F (-10 TO 60 C)
Storage Temperature Range	-40 TO 154.4 F (-40 TO 68 C)
Relative Humidity	10 TO 90% RH, NON-CONDENSING
CONNECTIONS	
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>