

Pre-Configured Unshielded Cat6 6-Port Surface-Mount Box, 110 IDC, RJ45, White

MODEL NUMBER: N236-006-WH



Pre-configured self-contained Cat6 surface-mount box provides up to six RJ45 connections in applications where in-wall installation is impossible. Recommended for audio/video, voice and Ethernet applications.

Description

The N236-006-WH Pre-Configured Unshielded Cat6 6-Port Surface-Mount Box features six RJ45 female connectors as a safe, easy, cost-effective tool for expanding your Cat5e/6 audio/video, voice or Ethernet network. The ABS UL 94V-0 flame-retardant housing mounts practically anywhere, including a wall or baseboard, using the included mounting screws or double-sided adhesive tape.

Just snap open the top cover to terminate up to six 22–26 AWG Cat5e/6 copper cables using a standard 110 IDC punchdown tool (such as Tripp Lite's N046-000). The termination blocks are color-coded for easy T568A or T568B wiring. Zip ties are included for neatly securing the cables to the Cat6 surface-mount box, which features rear routing slots to allow the box to be installed flush against a wall or ceiling.

Snap the cover back on, and connect up to six Cat5e/6 cables to the pre-installed RJ45 keystone jacks with 50-micron gold-plated contacts for maximum conductivity and minimum data loss. The N236-006-WH offers great flexibility in placement, especially in applications where in-wall box and wire installation is impossible.

Features

6-Port Surface-Mount Box Completes A/V, Voice and Ethernet Applications

- Connect up to 6 Cat5e/6 cables to pre-installed RJ45 keystone jacks
- 50 m gold-plated contacts for maximum conductivity
- Durable ABS UL 94V-0 flame-retardant housing designed to last
- Complies with ANSI/TIA/EIA 568B standards

Ideal for Applications in Which In-Wall Installation Is Impossible

Highlights

- Uses standard 110 IDC punchdown termination
- Recommended for use with 22–26 AWG Cat5e/6 cabling
- Termination blocks color-coded for T568A/B wiring compatibility
- Durable ABS UL 94V-0 flame-retardant housing designed to last
- 6 RJ45 jacks with gold-plated contacts for maximum conductivity

Package Includes

- N236-006-WH Pre-Configured Unshielded Cat6 6-Port Surface-Mount Box
- (2) Double-sided tape
- (6) Cable ties
- (2) Mounting screws
- Quick Start Guide



- Recommended for use with 22–26 AWG Cat5e/6 cabling
- Uses standard 110 IDC punchdown termination
- Termination blocks color-coded for T568A/B wiring compatibility
- Zip ties included for neatly securing cables through rear routing slots

Easy to Mount Almost Anywhere

- Mounting screws and double-sided tape are included

Specifications

OVERVIEW	
UPC Code	037332206961
Technology	Cat5/5e; Cat6
PHYSICAL	
Color	White
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>