

## Cat5e/6 Unshielded Surface-Mount Junction Box, 110 IDC, TAA

MODEL NUMBER: N237-001



Fast, easy, cost-effective way to directly connect 2 Cat5e/6 cables without using couplers or connectors. Ideal for audio/video, voice and Ethernet applications.

### Description

The N237-001 Cat5e/6 Unshielded Surface-Mount Junction Box is a fast, easy, cost-effective method of directly connecting two Cat5e/6 cables without using couplers or connectors. Designed for completing audio/video, voice and Ethernet applications, this junction box comes with screws and double-sided adhesive tape for quick mounting, as well as cable ties for keeping the cables neat and secure. It's made from ABS UL 94V-0 plastic and is recommended for use with solid conductor cable. The UL-listed box is color-coded for 568A/B wiring for easy 110 punchdown termination.

### Features

#### Completes A/V, Voice and Ethernet Applications

- Directly connects 2 Cat5e/6 cables without couplers or connectors
- Uses standard 110 punchdown termination
- Recommended for use with solid conductor cable
- Color-coded for 568A/B wiring
- Mounting hardware and cable ties included
- Durable ABS UL 94V-0 plastic housing

#### TAA-Compliant

- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332197313

### Highlights

- Uses standard 110 punchdown termination
- Recommended for use with solid conductor cable
- Color-coded for 568A/B wiring
- Mounting hardware and cable ties included
- Durable ABS UL 94V-0 plastic housing

### Package Includes

- N237-001 Cat5e/6 Unshielded Surface-Mount Junction Box
- Mounting hardware
- (2) Nylon cable ties



Powering Business Worldwide



Technology	Cat5/5e; Cat6
<b>CONNECTIONS</b>	
Side A - Connector 1	110 IDC
Side B - Connector 1	110 IDC
<b>PHYSICAL</b>	
Color	White
Total Number of Ports	0
Shipping Dimensions (hwd / in.)	0.02 x 4.53 x 4.44
Shipping Dimensions (hwd / cm)	0.06 x 11.51 x 11.28
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.