

Cat5e/6 Shielded Surface-Mount Junction Box, 110 IDC, TAA

MODEL NUMBER: **N237-001-SH**



Fast, easy, cost-effective way to directly connect 2 Cat5e/6 cables without using couplers or connectors. Ideal for audio/video, voice and Ethernet applications.

Description

The N237-001-SH Cat5e/6 Shielded Surface-Mount Junction Box is a fast, easy, cost-effective method of directly connecting two Cat5e/6 cables without using couplers or connectors. Designed for completing audio/video, voice and Ethernet applications, this junction box comes with screws and double-sided adhesive tape for quick mounting, as well as cable ties for keeping the cables neat and secure. It's made from ABS UL 94V-0 plastic and is recommended for use with solid conductor cable. The UL-listed box is color-coded for 568A/B wiring for easy 110 punchdown termination. The shielded N237-001-SH protects the signal against EMI/RFI line noise and has a dedicated space on the punchdown block for grounding.

Features

Completes A/V, Voice and Ethernet Applications

- Directly connects 2 Cat5e/6 cables without couplers or connectors
- Uses standard 110 punchdown termination
- Recommended for use with solid conductor cable
- Protects against EMI/RFI line noise
- Dedicated space on punchdown block for grounding
- Color-coded for 568A/B wiring
- Mounting hardware and cable ties included
- Durable ABS UL 94V-0 plastic housing

TAA-Compliant

- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Uses standard 110 punchdown termination
- Recommended for use with solid conductor cable
- Color-coded for 568A/B wiring
- Protects against EMI/RFI line noise
- Dedicated space on punchdown block for grounding

Package Includes

- N237-001-SH Cat5e/6 Shielded Surface-Mount Junction Box
- Mounting hardware
- (2) Nylon cable ties



Specifications

OVERVIEW	
UPC Code	037332197320
PHYSICAL	
Shipping Dimensions (hwd / in.)	0.25 x 4.90 x 4.09
Shipping Dimensions (hwd / cm)	0.64 x 12.45 x 10.39
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
Color	Silver
FEATURES & SPECIFICATIONS	
Technology	Cat5/5e; Cat6
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>