

## Toolless Cat6a Keystone Jack, PoE/PoE+ Compliant, Shuttered - Gray, TAA

MODEL NUMBER: N238-001-GY-TFA



Terminate your Cat6a wall jack without using a punchdown tool. Ideal for standard keystone wallplates, patch panels and surface-mount boxes.

### Description

Strengthen your high-speed network with Tripp Lite's N238-001-GY-TFA Toolless Cat6a Keystone Jack. Terminate your Cat6a wall jack without using a punchdown tool. Just lace the conductors into the stuffer cap, press the 110 connector, and lock the jack into place. Use in standard keystone wallplates, patch panels and surface-mount boxes. RJ45 port is compatible with all Cat6a cables, and toolless punchdown connection is compatible with 22-24AWG Solid wire cabling. Power over Ethernet Plus (PoE+) compliant.

### Features

**Strengthens Your High-Speed Network** Ideal for standard keystone wallplates, patch panels and surface-mount boxes Lets you terminate your Cat6a wall jack without using a punchdown tool Toolless punchdown connection compatible with 22-24AWG Solid Wire cabling RJ45 port compatible with all Cat6a cables Power over Ethernet Plus (PoE+) compliant, specially designed to prevent spark-gap erosion

**Superior Construction for Superior Performance** UL-listed Meets all EIA/TIA Cat6a requirements Features a shutter / dust cap that protects from dust and contaminants when not in use

**TAA-Compliant** Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchasing

## Specifications

OVERVIEW	
UPC Code	037332189950
Product Type	Tool-Free
Technology	Cat5/5e; Cat6; Cat6a
PHYSICAL	

### Highlights

- Easy to terminate—no punchdown tool required
- Features a shutter / dust cap that protects from dust and contaminants when not in use
- RJ45 port compatible with all Cat6a cables
- Toolless punchdown connection compatible with 22-24AWG Solid Wire cabling
- Power over Ethernet Plus (PoE+) compliant, specially designed to prevent spark-gap erosion
- Meets all EIA/TIA Cat6a requirements

### Package Includes

- N238-001-GY-TFA Toolless Cat6a Keystone Jack, PoE+ Compliant, Gray

Color	Gray
Connector Color	Gray
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
<b>CONNECTIONS</b>	
Number of Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	110 IDC
PoE Type	Type 4 High-Power (100W, IEEE 802.3bt)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty