

## Toolless Cat6a Keystone Jack, PoE/PoE+ Compliant, Shuttered - Gray, TAA

MODEL NUMBER: N238-001-GY-TFA



Terminate your Cat6a wall jack without using a punchdown tool. Ideal for standard keystone wallplates, patch panels and surface-mount boxes.

### Description

Strengthen your high-speed network with Tripp Lite's N238-001-GY-TFA Toolless Cat6a Keystone Jack. Terminate your Cat6a wall jack without using a punchdown tool. Just lace the conductors into the stuffer cap, press the 110 connector, and lock the jack into place. Use in standard keystone wallplates, patch panels and surface-mount boxes. RJ45 port is compatible with all Cat6a cables, and toolless punchdown connection is compatible with 22-24AWG Solid wire cabling. Power over Ethernet Plus (PoE+) compliant.

### Features

**Strengthens Your High-Speed Network** Ideal for standard keystone wallplates, patch panels and surface-mount boxes Lets you terminate your Cat6a wall jack without using a punchdown tool Toolless punchdown connection compatible with 22-24AWG Solid Wire cabling RJ45 port compatible with all Cat6a cables Power over Ethernet Plus (PoE+) compliant, specially designed to prevent spark-gap erosion

**Superior Construction for Superior Performance** UL-listed Meets all EIA/TIA Cat6a requirements Features a shutter / dust cap that protects from dust and contaminants when not in use

**TAA-Compliant** Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchasing

### Highlights

- Easy to terminate—no punchdown tool required
- Features a shutter / dust cap that protects from dust and contaminants when not in use
- RJ45 port compatible with all Cat6a cables
- Toolless punchdown connection compatible with 22-24AWG Solid Wire cabling
- Power over Ethernet Plus (PoE+) compliant, specially designed to prevent spark-gap erosion
- Meets all EIA/TIA Cat6a requirements

### Package Includes

- N238-001-GY-TFA Toolless Cat6a Keystone Jack, PoE+ Compliant, Gray

## Specifications

OVERVIEW	
UPC Code	037332189950
Technology	Cat5/5e; Cat6; Cat6a
PHYSICAL	
Color	Gray



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Weight (kg)	0.02
Shipping Weight (lbs.)	0.04
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	110 IDC
PoE Type	Type 3 PoE++/UPoE (60W, IEEE 802.3bt)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>