

Cat6/Cat5e 110 Style Punch Down Keystone Jack - Yellow, TAA

MODEL NUMBER: N238-001-YW



Highlights

- Use in Cat6 or Cat5e installations
- Compliant with EIA/TIA CAT6 connecting hardware specifications.
- Dual-color coded labeling made for both 568A and 568B (258A) wiring schemes.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Yellow Cat6/Cat5e 110 Punch Down Keystone Jack
- Termination caps (2)

Description

These Cat6/Cat5e 110-Style Punch-Down Keystone Jacks provide maximum flexibility for any UTP Ethernet environment. Ideal for Cat5e cabling environments, the jack also meets UL-certified ANSI/TIA/EIA-568-B.2-1 Permanent Link/Channel Identification Test for Cat6 cabling installations. The uniquely patterned printed circuit board construction is designed to meet Cat6 250 MHz performance, and is fully compliant with EIA/TIA CAT6 connecting hardware specifications. With its compact casing, it fits into any conventional face plate, outlet box or panel. It also features dual-color-coded labeling made for both 568A and 568B (258A) wiring schemes.

UTP Cat6 22-24 AWG solid cable

Features

- Use in Cat6 or Cat5e installations
- Compliant with EIA/TIA Cat6 connecting hardware specifications
- Dual-color coded labeling made for both 568A & 568B (258A) wiring schemes
- Compact casing fits into any conventional face plate, outlet box, or panel
- UL-certified ANSI/TIA/EIA-568-B.2-1 Permanent Link/Channel Identification Test
- Uniquely patterned, printed circuit board designed to meet Cat6 performances
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332153586
Product Type	RJ45 Keystone Jack
Technology	Cat5/5e; Cat6
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

Number of Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	110 IDC
PHYSICAL	
Color	Yellow
Connector Color	Yellow
Shipping Dimensions (hwd / in.)	0.25 x 0.25 x 0.50
Shipping Dimensions (hwd / cm)	0.64 x 0.64 x 1.27
Shipping Weight (lbs.)	0.03
Shipping Weight (kg)	0.01
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.