

Cat6/Cat5e 110 Style Punch Down Keystone Jack - Blue, 25-Pack, TAA

MODEL NUMBER: N238-025-BL



Highlights

- 25-Pack
- Use in Cat6 or Cat5e installations
- Compliant with EIA/TIA CAT6 connecting hardware specifications.
- Dual-color coded labeling made for both 568A & 568B (258A) wiring schemes.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Cat6/Cat5e 110 Punch Down Keystone Jack - Blue, 25-Pack
- Termination Caps (x25)

Description

This Cat6/Cat5e 110-Style Punch-Down Keystone Jack provides maximum flexibility for any UTP Ethernet environment. Ideal for Cat5e cabling environments, the jack also meets UL-certified ANSI/TIA/EIA-568-B.2-1 Permanent Link/Channel Identification Test for Cat6 cabling installations. The uniquely patterned printed circuit board construction is designed to meet Cat6 250 MHz performance, and is fully compliant with EIA/TIA Cat6 connecting hardware specifications. With its compact casing, it fits into any conventional face plate, outlet box or panel. It also features dual-color-coded labeling made for both 568A and 568B (258A) wiring schemes.
 UTP Cat6 22-24 AWG solid cable

Features

- 25-Pack
- Use in Cat6 or Cat5e installations
- Compliant with EIA/TIA Cat6 connecting hardware specifications
- Dual-color coded labeling made for both 568A & 568B (258A) wiring schemes
- Compact casing fits into any conventional face plate, outlet box, or panel
- UL-certified ANSI/TIA/EIA-568-B.2-1 Permanent Link/Channel Identification Test
- Uniquely patterned, printed circuit board designed to meet Cat6 performances
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

| OVERVIEW | |
|--------------|--------------------|
| UPC Code | 037332187840 |
| Product Type | RJ45 Keystone Jack |
| Technology | Cat5/5e; Cat6 |
| CONNECTIONS | |



Powering Business Worldwide



| | |
|-------------------------------------|----------------------------------|
| Number of Ports | 1 |
| Side A - Connector 1 | RJ45 (FEMALE) |
| Side B - Connector 1 | 110 IDC |
| PHYSICAL | |
| Color | Blue |
| Connector Color | Blue |
| Shipping Dimensions (hwd / in.) | 7.01 x 7.87 x 0.50 |
| Shipping Dimensions (hwd / cm) | 17.81 x 19.99 x 1.27 |
| Shipping Weight (lbs.) | 0.48 |
| Shipping Weight (kg) | 0.22 |
| Unit Dimensions (hwd / in.) | 7.010 x 7.870 x 0.500 |
| STANDARDS & COMPLIANCE | |
| Product Certifications | UL 1863; UL 2043 |
| Product Compliance | RoHS; Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.