



12-Port Cat6/Cat5 Wall-Mount Vertical 110 Patch Panel, TAA

MODEL NUMBER: N250-012









Highlights

- 12-port vertical wall-mount
- 110 punch down termination
- Includes 89D mounting bracket
- Cat6 Certified
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Cat6 Wall Mount Patch Panel 568B-12 Port w/bracket
- · 2 mounting screws
- Pkg wire ties
- Instruction Sheet

Description

This Cat6 wall-mount patch panel guarantees compatibility with all networks. Color-coded for both EIA/TIA 568a and 568b installations. Panel comes with 110-type termination blocks. This 12-inch panel effortlessly mounts to a wall or desk with two "C" brackets. Mounting bracket is provided. UTP Cat6 22-24 AWG solid cable

Features

- CAT6 Rated/Certified
- UL Approved
- 110 punch down termination
- Ports clearly numbered both on front and back
- Labels on front enable each port to be named.
- Color-coded label on back offers both EIA/TIA 568A & 568B wiring
- Metal frame
- Includes mounting bracket

Specifications

| OVERVIEW | |
|----------------------|---------------|
| UPC Code | 037332131034 |
| Product Type | Wall Mount |
| Technology | Cat5/5e; Cat6 |
| CONNECTIONS | |
| Number of Ports | 12 |
| Side A - Connector 1 | 110 IDC |





| Side B - Connector 1 | RJ45 (FEMALE) | |
|-------------------------------------|---------------------------------------|--|
| PoE Type | Type 2 PoE+ (30W, IEEE 802.3at) | |
| 1 02 1)p0 | 1 1990 2 1 02 1 (0011), 1222 002.000y | |
| PHYSICAL | | |
| Shipping Dimensions (hwd / in.) | 11.02 x 3.15 x 2.17 | |
| Shipping Dimensions (hwd / cm) | 27.99 x 8.00 x 5.51 | |
| Shipping Weight (lbs.) | 0.68 | |
| Shipping Weight (kg) | 0.31 | |
| Unit Dimensions (hwd / in.) | 3.330 x 10.000 x 1.900 | |
| Unit Dimensions (hwd / cm) | 8.382 x 25.4 x 4.82 (with bracket) | |
| Panel Style | Punchdown | |
| | | |
| STANDARDS & COMPLIANCE | | |
| Product Compliance | RoHS; Trade Agreements Act (TAA) | |
| | | |
| WARRANTY & SUPPORT | | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty | |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.